



APC Replacement Battery Cartridge #45
Part Number: RBC45



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	--
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

Physical

Net Weight	3.74 lbs. (1.70 kg)
Maximum Height	4.40 inches (112 mm)
Maximum Width	3.90 inches (99 mm)
Maximum Depth	2.93 inches (74 mm)
Shipping Weight	4.30 lbs. (1.95 kg)
Shipping Width	7.00 inches (178 mm)
Shipping Height	6.25 inches (159 mm)
Shipping Depth	7.25 inches (184 mm)

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
-----------------------	-------------------------

Operating Relative Humidity 0 - 95%
Operating Elevation 0-10000 feet (0-3000 meters)
Storage Temperature 5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity 0 - 95%
Storage Elevation 0-50000 feet (0-15000 meters)
Conformance
Standard Warranty 1 year repair or replace
Sustainable Offer Status
PEP Available in Documentation tab
EOLI Available in Documentation tab

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.