



APC Replacement Battery Cartridge #47
Part Number: RBC47



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Output

battoutvolt
12.0

battoutmah
3200

Batteries & Runtime

Battery Volt-Amp-Hour Capacity
36

Battery Type
Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof

Battery mounting
--

Expected Battery Life (years)
3 - 5

RBC™ Quantity
1

Physical

Net Weight
3.08 lbs. (1.40 kg)

Maximum Height
2.60 inches (66 mm)

Maximum Width
2.64 inches (67 mm)

Maximum Depth
5.28 inches (134 mm)

Shipping Weight
3.68 lbs. (1.67 kg)

Shipping Width
5.75 inches (146 mm)

Shipping Height
3.70 inches (94 mm)

Shipping Depth
7.37 inches (187 mm)

Color
Black

Environmental

Operating Environment
32 - 104 °F (0 - 40 °C)

Operating Relative Humidity

| |
|---|
| 0 - 95% |
| Operating Elevation 0-10000 feet (0-3000 meters) |
| Storage Temperature 5 - 113 °F (-15 - 45 °C) |
| Storage Relative Humidity 0 - 95% |
| Storage Elevation 0-50000 feet (0-15000 meters) |
| Conformance |
| Standard Warranty 30 days (Japan only) |
| Sustainable Offer Status |
| PEP Available in Documentation tab |
| EOLI Available in Documentation tab |

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.