

You are here: Home > Products > Uninterruptible Power Supply (UPS) > Smart-UPS On-Line

Smart-UPS On-Line

APC Smart-UPS RT 3000VA Rack Tower 208V



APC Smart-UPS On-Line,2100 Watts /3000 VA,Input 208V /Output 208V, Interface Port RJ-45 10 Base-T, SmartSlot, Extended runtime model, Rack Height 3 U

Includes: CD with software, Rack Mounting support rails, Smart UPS signalling RS-232 cable, User Manual

Standard Lead Time: Usually in Stock

SURTD3000RMXLT3U

Email Technical Specifications

Printer Friendly

Product Category

Computer and Peripheral (6) Home UPS (1) Network and Server


> Smart-UPS

- > Smart-UPS BR
- > Smart-UPS On-Line
- > Symmetra

Data Center and Facility 3 Phase (15)


Special Applications (5)
UPS Management (7)

Return to Uninterruptible Power Supply (UPS)



replacement battery	INDUTT	
RBC™ Quantity	1	
Extended Run Options	APC Smart-UPS RT 3000VA Rack Tower 208V	
Runtime Graph		

Curve	Part Number(s)
А	SURTD3000RMXLT3U
В	SURTD3000RMXLT3U + (1)SURT192RMXLBP3U
С	SURTD3000RMXLT3U + (2)SURT192RMXLBP3U
D	SURTD3000RMXLT3U + (3)SURT192RMXLBP3U
Е	SURTD3000RMXLT3U + (4)SURT192RMXLBP3U



Hover over the line on the graph above to view the runtime at any desired load

Curve fit to measured runtime data. All measurements taken with new, fully charged batteries, at typical environmental conditions, with no electrical input and balanced resistive load (PF = 1.0) output.

View Enlarged Graph

View Runtime Chart

C			0	B //	
Comi	nun	icarioi	1S &	IVIana	agement

Storage Temperature

-15 - 45 °C

Communications & Manageme	ent
Interface Port(s)	RJ-45 10 Base-T, SmartSlot
Available SmartSlot™ Interface Qu	uantity 1
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : Overload and Bypass Indicators
Audible Alarm	Alarm when on battery: distinctive low battery alarm: overload continuous tone alarm
Emergency Power Off (EPO)	Yes
Surge Protection and Filtering	1
Surge energy rating	480 Joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449
Physical	
Maximum Height	130.00 mm
Maximum Width	432.00 mm
Maximum Depth	660.00 mm
Rack Height	3U
Net Weight	54.55 KG
Shipping Weight	63.64 KG
Shipping Height	347.00 mm
Shipping Width	603.00 mm
Shipping Depth	980.00 mm
Color	Black
Units per Pallet	6.00
Environmental	
Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters

Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters
Audible noise at 1 meter from sur unit	face of 55.00 dBA
Online Thermal Dissipation	636.00 BTU/hr
Conformance	
Conformance Regulatory Approvals	CSA, FCC Part 15 Class A, OSHPD, UL 1778
	CSA, FCC Part 15 Class A, OSHPD, UL 1778 2 years repair or replace
Regulatory Approvals	

^{**}The time to recharge to 90% of full battery capacity following a discharge to shutdown using a load rated for 1/2 the full load rating of the UPS.