

Share:



AP9881



Description: Wide selection of Rack PDU power cords for a variety of IT equipment.

Product Overview

Technical Specifications

Documentation

Output

[Print Technical Specification](#)

Maximum Total Current Draw 10

Input

Input Connections IEC-320 C14

Cord Length 0.61meters

Number of Power Cords 1

Maximum Line Current 10A

Physical

Net Weight 0.36KG

Shipping weight 0.46KG

Shipping Height 305mm , 30.5CM

Shipping Width 102mm , 10.2CM

Shipping Depth 102mm , 10.2CM

Color Black

Conformance

Standard warranty 2 years repair or replace

Sustainable Offer Status

RoHS Compliant

PEP Available in Documentation tab

EOLI Available in Documentation tab