

Select Your Country/Region

Search

HomeProductsSupportServicesSelectorsHow to Buy

Remote UPS Power-Off Device

Immediately turns off the power output of connected APC UPSs.

Includes: DB9-DB9 Cable, Keystone Jack, Mounting pads, RJ11 Cable, User Manual

Part Number: AP9830

Compare Models

Email Technical Specifications

Printer Friendly

Additional Information

Product Overview
User Manual & Installation Guides
Product Distribution



Technical Specifications

□ Physical	
Net Weight	0.50 lbs. (0.23 kg)
Maximum Height	1.00 inches (25 mm)
Maximum Width	3.75 inches (95 mm)
Maximum depth	2.38 inches (60 mm)
Shipping Weight	0.80 lbs. (0.36 kg)
Shipping Height	2.86 inches (73 mm)
Shipping Width	9.50 inches (241 mm)
Shipping Depth	6.50 inches (165 mm)
Color	Beige
Units per Pallet	672.00

Environmental

Operating Environment	0 - 45 °C (32 - 113 °F)
Storage Temperature	-15 - 65 °C (5 - 149 °F)
Operating Relative Humidity	0 - 95%
Storage Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Elevation	0-50000 feet (0-15000 meters)

□ Conformance

Regulatory Approvals	CE,EN 55024,EN 55082
Standard Warranty	2 years repair or replace

<u>Copyright</u> © American Power Conversion Corp., all rights reserved <u>About APCInvestorsJob SeekersPressFeedbackContactPrivacy Policy</u>

Options:

O Interface Connections

Features:

- O Multiple System Shutdown
- O Remote power-off
- Switch Compatibility
- O UPS signal support