

HomeProductsSupportServicesSelectorsHow to Buy

INI

APC Replacement Battery Cartridge #2

Includes: All required connectors, Authorized Return Service (ARS) tag (currently available in the US only), Battery recycling guide, Installation Guide, Reusable packaging

Part Number : RBC2

Email Technical Specifications

Additional Information User Manual & Installation Guides Product Distribution



[+] More Images

Technical Specifications

Batteries & Runtime		Features:
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof	 ₀ Hot Swap Batteries _ ₀ Plug-and-Play
Battery mounting		installation
Expected Battery Life (years)	3 - 5	motanation
RBC™ Quantity	1	
Physical		
Net Weight	5.50 lbs. (2.50 kg)	
Maximum Height	1.90 inches (48 mm)	
Maximum Width	4.00 inches (102 mm)	
Maximum depth	5.50 inches (140 mm)	
Shipping Weight	6.10 lbs. (2.77 kg)	
Shipping Width	6.90 inches (175 mm)	
Shipping Height	3.50 inches (89 mm)	
Shipping Depth	8.40 inches (213 mm)	
Color	Black	
Units per Pallet	150.00	
Environmental		
Operating Environment	0 - 40 °C (32 - 104 °F)	
Operating Relative Humidity	0 - 95%	
Operating Elevation	0-10000 feet (0-3000 meters)	
Storage Temperature	-15 - 45 °C (5 - 113 °F)	
Storage Relative Humidity	0 - 95%	
Storage Elevation	0-50000 feet (0-15000 meters)	
Conformance		
Standard Warranty	1 year repair or replace	

Copyright © American Power Conversion Corp., all rights reserved

About APCInvestorsJob SeekersPressFeedbackContactPrivacy Policy

Search