

APC Replacement Battery Cartridge #4

Includes: All required connectors, Authorized Return Service (ARS) tag (currently available in the US only), Battery recycling guide, Installation Guide, Reusable packaging

Part Number : **RBC4**

- [Email Technical Specifications](#)
- [Printer Friendly](#)

- Additional Information**
- [User Manual & Installation Guides](#)
 - [Product Distribution](#)



[+] More Images

Technical Specifications

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	--
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

Features:

- o Hot Swap Batteries
- o Plug-and-Play installation

Physical

Net Weight	8.10 lbs. (3.68 kg)
Maximum Height	3.90 inches (99 mm)
Maximum Width	3.70 inches (94 mm)
Maximum depth	5.90 inches (150 mm)
Shipping Weight	8.80 lbs. (4.00 kg)
Shipping Width	6.90 inches (175 mm)
Shipping Height	4.90 inches (124 mm)
Shipping Depth	8.40 inches (213 mm)
Color	Black
Units per Pallet	100.00

Environmental

Operating Environment	0 - 40 °C (32 - 104 °F)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-15 - 45 °C (5 - 113 °F)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Standard Warranty	1 year repair or replace
-------------------	--------------------------