

#### Select Your Country/Region

## **Search**

HomeProductsSupportServicesSelectorsHow to Buy

## APC Replacement Battery Cartridge #6

Includes: All required connectors, Authorized Return Service (ARS) tag (currently available in the US only), Battery recycling guide, Installation Guide, Reusable packaging

Part Number : RBC6

**Email Technical Specifications** 

Printer Friendly

**Additional Information** 

User Manual & Installation Guides

Product Distribution



[+] More Images

# **Technical Specifications**

### ☐ Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte: leakproof
Battery mounting	
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1

# ☐ Physical

Net Weight	16.90 lbs. (7.68 kg)
Maximum Height	3.70 inches ( 94 mm)
Maximum Width	6.00 inches (152 mm)
Maximum depth	7.70 inches (196 mm)
Shipping Weight	18.60 lbs. ( 8.45 kg)
Shipping Width	10.20 inches (259 mm)
Shipping Height	6.90 inches (175 mm)
Shipping Depth	11.90 inches (302 mm)
Color	Black
Units per Pallet	60.00

#### ☐ Environmental

Operating Environment	0 - 40 °C (32 - 104 °F)
Operating Relative Humidity	0 - 95%
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-15 - 45 °C (5 - 113 °F)
Storage Relative Humidity	0 - 95%
Storage Elevation	0-50000 feet (0-15000 meters)

#### Features:

- O Hot Swap Batteries
- O Plug-and-Play installation



Standard Warranty

1 year repair or replace

Copyright © American Power Conversion Corp., all rights reserved About APCInvestorsJob SeekersPressFeedbackContactPrivacy Policy