

8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

D

PART	JA CKET	LENGTH		PART	JA CKET	LENGTH		PART	JACKET	JACKET LENGTH	
NUMBER	COLOR	FEET	METERS	NUMBER	COLOR	FEET	METERS	NUMBER	COLOR	FEET	METERS
TRD855SIG-1	GRAY	1.0	0. 31	TRD855SIGBLK-1	BLACK	1.0	0. 31	TRD855SIGRD-1	RED	1.0	0. 31
TRD855SIG-2	GRAY	2.0	0.61	TRD855SIGBLK-2	BLACK	2.0	0.61	TRD855SIGRD-2	RED	2.0	0.61
TRD855SIG-3	GRAY	3.0	0.91	TRD855SIGBLK-3	BLACK	3.0	0.91	TRD855SIGRD-3	RED	3.0	0.91
TRD855SIG-5	GRAY	5.0	1.52	TRD855SIGBLK-5	BLACK	5.0	1.52	TRD855SIGRD-5	RED	5.0	1.52
TRD855SIG-7	GRAY	7.0	2.13	TRD855SIGBLK-7	BLACK	7.0	2.13	TRD855SIGRD-7	RED	7.0	2.13
TRD855SIG-10	GRAY	10.0	3.05	TRD855SIGBLK-10	BLACK	10.0	3.05	TRD855SIGRD-10	RED	10.0	3.05
TRD855SIG-15	GRAY	15.0	4.57	TRD855SIGBLK-15	BLACK	15.0	4.57	TRD855SIGRD-15	RED	15.0	4.57
TRD855SIG-20	GRAY	20.0	6.10	TRD855SIGBLK-20	BLACK	20.0	6.10	TRD855SIGRD-20	RED	20.0	6.10
TRD855SIG-25	GRAY	25.0	7.62	TRD855SIGBLK-25	BLACK	25.0	7.62	TRD855SIGRD-25	RED	25.0	7.62
TRD855SIG-30	GRAY	30.0	9.14	TRD855SIGBLK-30	BLACK	30.0	9.14	TRD855SIGRD-30	RED	30.0	9.14
TRD855SIG-40	GRAY	40.0	12.19	TRD855SIGBLK-40	BLACK	40.0	12.19	TRD855SIGRD-40	RED	40.0	12.19
TRD855SIG-50	GRAY	50.0	15.24	TRD855SIGBLK-50	BLACK	50.0	15.24	TRD855SIGRD-50	RED	50.0	15.24
TRD855SIG-60	GRAY	60.0	18.29	TRD855SIGBLK-60	BLACK	60.0	18.29	TRD855SIGRD-60	RED	60.0	18.29
TRD855SIG-75	GRAY	75.0	22.86	TRD855SIGBLK-75	BLACK	75.0	22.86	TRD855SIGRD-75	RED	75.0	22.86
TRD855SIG-80	GRAY	80.0	24.38	TRD855SIGBLK-80	BLACK	80.0	24.38	TRD855SIGRD-80	RED	80.0	24.38
TRD855SIG-90	GRAY	90.0	27.43	TRD855SIGBLK-90	BLACK	90.0	27.43	TRD855SIGRD-90	RED	90.0	27.43
TRD855SIG-100	GRAY	100.0	30.48	TRD855SIGBLK-100	BLACK	100.0	30.48	TRD855SIGRD-100	RED	100.0	30.48
TRD855SIG-150	GRAY	150.0	45.72	TRD855SIGBLK-150	BLACK	150.0	45.72	TRD855SIGRD-150	RED	150.0	45.72
TRD855SIG-200	GRAY	200.0	60.96	TRD855SIGBLK-200	BLACK	200.0	60.96	TRD855SIGRD-200	RED	200.0	60.96
TRD855SIG-250	GRAY	250.0	76.20	TRD855SIGBLK-250	BLACK	250.0	76.20	TRD855SIGRD-250	RED	250.0	76.20
TRD855SIG-300	GRAY	300.0	91.44	TRD855SIGBLK-300	BLACK	300.0	91.44	TRD855SIGRD-300	RED	300.0	91.44



8 7 6 5 7 4 3