

8 REVISIONS THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE REV DESCRIPTION DATE APPROVED WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED. H FCN 3037: ADDED "BLACK" TO SNAGLESS BOOT MATERIAL NOTE 10/5/07 DRC ECN3191: ADDED 20, 30, 40, 60, 80 & 90 FT LENGTHS 02/06/08 D PARHAM ECN3320: ADDED PACKAGED ON A SPOOL NOTE, UPDATED FORMAT, 05/07/08 D. PARHAM ECN3552: ADDED RED & BLK CABLES. MODIFIED PACKAGING NOTE 09/03/08 D. PARHAM D PART **JACKET** LENGTH PART JA CKET **LENGTH** PART **JACKET** LENGTH COLOR NUMBER COLOR **FEET** NUMBER COLOR **FEET METERS** NUMBER **FEET METERS METERS** GRAY 1.0 0.31 TRD855SIGBLK-1 BLACK 1.0 TRD855SIGRD-1 1.0 0.31 TRD855SIG-1 0.31 RED TRD855SIG-2 **GRAY** 2.0 0.61 TRD855SIGBLK-2 **BLACK** 2.0 TRD855SIGRD-2 RED 2.0 0.61 0.61 GRAY 3.0 0.91 TRD855SIGBLK-3 **BLACK** 3.0 0.91 RED 3.0 0.91 TRD855SIG-3 TRD855SIGRD-3 TRD855SIG-5 TRD855SIGBLK-5 GRAY 5.0 1.52 BLACK 5.0 1.52 TRD855SIGRD-5 RED 5.0 1.52 TRD855SIG-7 GRAY 7.0 2.13 TRD855SIGBLK-7 BLACK 7.0 2.13TRD855SIGRD-7 RED 7.0 2.13 TRD855SIG-10 **GRAY** TRD855SIGBLK-10 BLACK 10.0 TRD855SIGRD-10 RED 10.0 10.0 3.05 3.05 3.05 TRD855SIG-15 GRAY 15.0 4.57 TRD855SIGBLK-15 **BLACK** 15.0 4.57 TRD855SIGRD-15 RED 15.0 4.57 C TRD855SIG-20 GRAY 20.0 6.10 TRD855SIGBLK-20 **BLACK** 20.0 6.10 TRD855SIGRD-20 RED 20.0 6.10 TRD855SIG-25 **GRAY** 25.0 7.62 TRD855SIGBLK-25 **BLACK** 25.0 7.62 TRD855SIGRD-25 RED 25.0 7.62 TRD855SIG-30 GRAY 30.0 9.14 TRD855SIGBLK-30 BLACK 30.0 9.14 TRD855SIGRD-30 RED 30.0 9.14 TRD855SIG-40 **GRAY** 40.0 12.19 TRD855SIGBLK-40 **BLACK** 40.0 12.19 RED 40.0 12.19 TRD855SIGRD-40 TRD855SIG-50 GRAY 50.0 15.24 TRD855SIGBLK-50 **BLACK** 50.0 15.24 TRD855SIGRD-50 RED 50.0 15.24 TRD855SIG-60 **GRAY** 60.0 18.29 TRD855SIGBLK-60 **BLACK** 60.018.29 TRD855SIGRD-60 RFD 60.018.29 TRD855SIGBLK-75 TRD855SIG-75 GRAY 75.0 22.86 BLACK 75.0 22.86 TRD855SIGRD-75 RED 75.0 22.86 TRD855SIG-80 GRAY 80.0 24.38 TRD855SIGBLK-80 **BLACK** 80.0 24.38 TRD855SIGRD-80 RED 80.0 24.38 TRD855SIG-90 GRAY 90.0 27.43 TRD855SIGBLK-90 BLACK 90.0 27.43 TRD855SIGRD-90 RED 90.0 27.43**GRAY BLACK** 100.0 30.48 RED 30.48 TRD855SIG-100 100.0 30.48 TRD855SIGBLK-100 TRD855SIGRD-100 100.0 TRD855SIG-150 GRAY 150.0 45.72 TRD855SIGBLK-150 **BLACK** 150.0 45.72 TRD855SIGRD-150 RED 150.0 45.72 200.0 200.0 200.0 TRD855SIG-200 GRAY 60.96 TRD855SIGBLK-200 BLACK 60.96 TRD855SIGRD-200 RED 60.96 TRD855SIG-250 **GRAY** 250.0 76.20 TRD855SIGBLK-250 **BLACK** 250.0 76.20 TRD855SIGRD-250 RED 250.0 76.20 TRD855SIG-300 **GRAY** 300.0 91.44 TRD855SIGBLK-300 BLACK 300.0 91.44 TRD855SIGRD-300 RED 300.0 91.44 45 BEECHWOOD DRIVE **APPROVALS** DATE UNLESS OTHERWISE SPECIFIED, -COM NORTH ANDOVER, MA DIMENSIONS ARE IN INCHES [mm] DRAWN RY CONNECTIVITY
PRODUCTS 01845 8/16/2000 D. PARHAM OVERALL CABLE LENGTH TOLERANCE: \$12 (305) = +1 (25) /-0 >12 (305) 560 11524 | +2 (51) /-0 >60 (1524) \$120 (3048) = +4 (102) /-0 >120 (3048) \$300 (7620) = +6 (152) /-0 >300 (7620) = +5% /-0% CATEGORY 8/17/2000 Z. WORONKO PROVED BY TELECOM/MODULAR z. woronko PRODUCT DESCRIPTION CONFIGURATION DETAILS OF ALL OTHER DIMENSIONAL TOLERANCES: UNDIMENSIONED FEATURES CATEGORY 5e PATCH CORD, LSZH MAY VARY .XX = .15PRO IECTION FSCM NO DWG. NO. RFV COLOR VARIATIONS 43321 TRD855SIG MAY OCCUR CAD FILE: TRD855SIG.SLDDRW SCALE: NONE SHEET 2 OF 2 8 3 7