#### SVGA HD15 M/M with Disconnect 50.0 ft


#### Features for this product

- SVGA video signal transmission in difficult routing situations
- Low profile disconnect and HD15 backshell allows routing through 3/4" conduit
- User defined hardware results in maximum mounting flexibility
- Three 75 Ohm coaxial cables assure optimum video signal transmission
- Available in 5 standard lengths from 15 to 75 ft



Now there is a solution to your difficult installation problems. This series features a fully populated DDC compliant assembly with (2) low profile HD15 male connectors and our Super Thin cable. An additional feature of this series is our unique user defined mounting hardware plus a low profile break connector. The low profile disconnect connector's small size allows routing through 3/4" conduit and other tight spaces that would not accommodate the size of a HD15 connector. Offered in standard lengths of 15, 20, 25, 50 and 75 feet with a 1 foot lead in length to the low profile connector.

Details for this Mo	onitor, Video product			
L-com Item #	CTLB3VGAMM-50T			
Manufacturer	L-com			
UPC #	822335018310			
RoHS Status	Partially RoHS Compliant Stock 🧭			







Solder Type Mini DIN 4 Connectors with Metal Cover For SVHS Assemblies BAC-MD4M SVHS Mini DIN 4 Connector, Male

BAC-MD4F

SVHS Mini DIN 4 Connector, Female

### Sulkhead Feed-Thru Adapter for SVHS Mini DIN 4 - Fits 1/2" Diameter D-hole

MD44E

Bulkhead Feed-Thru Adapter, Female / Female

## Bulk SVGA Cable - Double Shielded with (3) 75 Ohm Coaxial Lines Plus Conductors

This is the same bulk cable used in our premium grade SVGA assemblies. The three coaxial lines are double shielded enhancing video performance. In addition the bulk cable construction includes four 26AWG twisted pairs and two 26AWG conductors. Used in conjunction with our D-Sub connectors you can now fabricate your own SVGA cable assemblies. Color: Black.

CTL3VGA-250 CTL3VGA-500 SVGA Bulk Cable, 250.0 ft SVGA Bulk Cable, 500.0 ft

## Bulk Super Thin SVGA Cable - Double Shielded - (3) 75 Ohm Coaxial Lines Plus Conductors

This is the same bulk cable used in our Thinline series SVGA assemblies. The three coaxial lines are double shielded enhancing video performance. In addition the bulk cable construction includes nine stranded 30AWG conductors. Used in conjunction with our D-Sub connectors you can now fabricate your own Super Thin SVGA cable assemblies.

CTL3VGA-250T CTL3VGA-500T Super Thin SVGA Bulk Cable, 250.0 ft Super Thin SVGA Bulk Cable, 500.0 ft

## SVHS Bulk Cable - Dual 75 Ohm Coaxials - High Flex Round PVC Jacket

R1088-100 R1088-500 R1088-1K Bulk S-Video Cable, 100.0 ft Bulk S-Video Cable, 500.0 ft Bulk S-Video Cable, 1000.0 ft



BAC-MD4F

# Running CTLB cable through 3/4" conduit