## Premium Molded D-sub Cable, DB9 Male / Male, 2.5 ft

## Features for this product


- · Foil plus braid shield provides maximum protection against EMI/RFI
- Custom stamped steel internal enclosure provides 100% shielding and a robust strain relief
- Molded backshells provide durability and increased strength at cable entry point
- Gold plated contacts provide reliable connections with repeated mating cycles
- DB9 male to male connectors, lengths range from 2.5 ft. to 50 ft.



L-com's top of the line offering of D-sub cable assemblies provide maximum protection against data corrupting EMI/RFI. Double shielded cable (copper braid plus aluminum mylar foil) and a custom steel internal enclosure separate these cables from any off the shelf D-sub cable on the market. Ideal for any electrically noisy environment where fans, motors or switches are nearby. Custom lengths and pinouts are available with modest minimum requirements.

Details for this D-Subminiature product		
L-com Item #	CS2N9MM-2.5	
Manufacturer	L-com	
UPC #	822335012790	
RoHS Status	Partially RoHS Compliant Stock 🧭	

## 140 D-Subminiature > Premium Molded D-Sub Cable Assemblies



Premium	Molded	Cable,	DB25	Male /	Male, 5.0 ft
Premium	Molded	Cable,	DB25	Male /	Male, 6.0 ft
Premium	Molded	Cable,	DB25	Male /	Male, 10.0 ft
Premium	Molded	Cable,	DB25	Male /	Male, 12.0 ft
Premium	Molded	Cable,	DB25	Male /	Male, 15.0 ft
Premium	Molded	Cable,	DB25	Male /	Male, 25.0 ft
Premium	Molded	Cable,	DB25	Male /	Male, 50.0 ft
Premium	Molded	Cable,	DB25	Male /	Female, 2.5 ft
Premium	Molded	Cable,	DB25	Male /	Female, 5.0 ft
Premium	Molded	Cable,	DB25	Male /	Female, 6.0 ft
Premium	Molded	Cable,	DB25	Male /	Female, 10.0 ft
Premium	Molded	Cable,	DB25	Male /	Female, 12.0 ft
Premium	Molded	Cable,	DB25	Male /	Female, 15.0 ft
Premium	Molded	Cable,	DB25	Male /	Female, 25.0 ft
Premium	Molded	Cable,	DB25	Male /	Female, 50.0 ft