





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
E	ECN 99999: UPDATED DRAWING AND NEW FORMAT	2/8/10	D.FRISIELLO



RECOMMENDED PANEL OPENING  
(MAX PANEL THICKNESS: 0.06")



JACKSCROW & HEX STANDOFF SPECIFICATION

NOTES:

MATERIAL:  
SHELL: STEEL  
CONTACTS: COPPER ALLOY  
HARDWARE: BRASS  
INSULATOR: PBT FIBER REINFORCED (UL94V-0 RATED)



FINISH:  
SHELL: TIN/NICKEL PLATED  
CONTACTS: GOLD FLASH PLATED, 1-5µ INCHES  
HARDWARE: NICKEL PLATED

ELECTRICAL:  
CURRENT RATING: 3 AMP  
INSULATION RESISTANCE: 1000 MΩ MIN @500 VDC  
DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC (FOR ONE MINUTE)


MISCELLANEOUS:  
OPERATING TEMPERATURE RANGE: -55°C TO +105°C.  
ALL CONTACTS WIRED STRAIGHT THROUGH.  
COMPONENT SHALL BE TESTED FOR CONTINUITY.

LABELING:  
PANTONE 2945 BLUE. "L-COM" FONT MyriaMM ITALIC.  
"GENDER CHANGER" FONT ARIAL BOLD, TEXT HEIGHTS; .085"  
TEXT COLOR; WHITE.

PACKAGING:  
COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



GENDER CHANGER



RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE
	DRAWN BY R.CARRICK	09/28/2000
	CHECKED BY T.CLARK	09/28/2000
	APPROVED BY D.PARHAM	09/28/2000
DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	
ANGULAR TOLERANCES: ALL = ± 1°	COLOR VARIATIONS MAY OCCUR	
PROJECTION		

		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY: D-SUBMINIATURE			
PRODUCT DESCRIPTION: GENDER CHANGER, DB50 FEMALE/FEMALE			
SIZE: <b>B</b>	FSCM NO.: <b>43321</b>	DWG. NO.: <b>DGB50F</b>	REV.: <b>E</b>
SCALE: 2:1		CAD FILE: DGB50F.SLDDRW	SHEET 1 OF 1