


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/30/04	MCCORMICK
B	ECN# 2731 - ADDED ROHS STAMP	10/23/07	D.GRIFFIN
C	ECN 3957: CHANGE MAIL HOUSING FROM NYLON TO ABS, NEW FORMAT	4/22/09	D.FRISIELLO
D	ECN 4278: ADDED OPERATING TEMPERATURE RANGE AND PACKAGING	10/1/09	D.FRISIELLO



- NOTES:**
1. RECOMMENDED CABLE DIAMETER: 0.138 ϕ THRU 0.276 ϕ
 2. IP (INGRESS PROTECTION) RATING: 67.
 3. OPERATING TEMPERATURE RANGE: -40°C TO +105°C.
 4. COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

MATERIAL:
 GASKETS: EPDM
 BODY: NYLON
 HOUSING: ABS
 O-RING: SILICONE
 SEAL: EPDM
 SEALING NUT: NYLON
 THUMBSCREW: BRASS

FINISH:
 THUMBSCREW: NICKEL PLATE

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.02 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	01/28/2004			
	CHECKED BY D.PARHAM	01/28/2004	CATEGORY DATA CABLING		
	APPROVED BY R.CARRICK	01/28/2004	PRODUCT DESCRIPTION DB9 FEMALE WATERPROOF CONNECTOR		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. WPDB9S-KIT	REV. D
REF		SCALE: NONE	CAD FILE: WPDB9S-KIT.SLDDRW	SHEET 1 OF 1	