


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/30/04	MCCORMICK
B	ECN 3957: CHANGE MATL HOUSING FROM NYLON TO ABS, NEW FORMAT	4/22/09	D.FRISIELLO
C	ECN 4278: ADDED OPERATING TEMPERATURE RANGE AND PACKAGING	10/1/09	D.FRISIELLO



NOTES:

1. RECOMMENDED CABLE DIAMETER: 0.236 ϕ THRU 0.394 ϕ
2. IP (INGRESS PROTECTION) RATING: 67.
3. OPERATING TEMPERATURE RANGE: -40°C TO +105°C.
4. COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

MATERIALS:

GASKETS: EPDM
 BODY: NYLON
 HOUSING: ABS
 O-RING: SILICONE
 SEAL: EPDM
 SEALING NUT: NYLON
 THUMBSCREW: BRASS

FINISH:

THUMBSCREW: NICKEL PLATE

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.02 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1° PROJECTION 	APPROVALS	DATE	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	01/28/2004		
	CHECKED BY D.PARHAM	01/28/2004	PRODUCT DESCRIPTION WPDB15 MALE WATERPROOF CONNECTOR	
	APPROVED BY R.CARRICK	01/28/2004	SIZE A	FSCM NO. 43321
		SCALE: NONE		CAD FILE: WPDB15P-KIT.SLDDRW
			SHEET 1 OF 1	