


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/30/04	MCCORMICK
B	ECN 3957: CHANGE MATL HOUSING FROM NYLON TO ABS, NEW FORMAT	4/22/09	D.FRISIELLO
C	ECN 4278: ADDED OPERATING TEMPERATURE RANGE AND PACKAGING	10/1/09	D.FRISIELLO



**NOTES:**

1. RECOMMENDED CABLE DIAMETER: 0.236  $\phi$  THRU 0.394  $\phi$
2. IP (INGRESS PROTECTION) RATING: 67.
3. OPERATING TEMPERATURE RANGE: -40°C TO +105°C.
4. COMPONENT ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.



**MATERIALS:**

GASKETS: EPDM  
BODY: NYLON  
HOUSING: ABS  
O-RING: SILICONE  
SEAL: EPDM  
SEALING NUT: NYLON  
THUMBSCREW: BRASS

**FINISH:**

THUMBSCREW: NICKEL PLATE

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = $\pm 0.1$ .XX = $\pm 0.02$ .XXX = $\pm 0.005$  ANGULAR TOLERANCES: ALL = $\pm 1^\circ$	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	01/28/2004		
	CHECKED BY D.PARHAM	01/28/2004	CATEGORY DATA CABLING	
	APPROVED BY R.CARRICK	01/28/2004	PRODUCT DESCRIPTION DP25 FEMALE WATERPROOF CONNECTOR	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE <b>A</b>	FSCM NO. <b>43321</b>
COLOR VARIATIONS MAY OCCUR		DWG. NO. WPDB25S-KIT	REV. <b>C</b>	SCALE: NONE
		CAD FILE: WPDB25S-KIT.SLDDRW	SHEET 1 OF 1	