


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	01/30/04	MCCORMICK
B	ECN 3957: CHANGE MATL HOUSING FROM NYLON TO ABS, NEW FORMAT	4/22/09	D.FRISIELLO



- NOTES:**
1. RECOMMENDED CABLE DIAMETER: 0.138  $\phi$  THRU 0.276  $\phi$
  2. IP (INGRESS PROTECTION) RATING: 67

**MATERIALS:**  
 GASKETS: EPDM  
 BODY: NYLON  
 HOUSING: ABS  
 O-RING: SILICONE  
 SEAL: EPDM  
 SEALING NUT: NYLON  
 THUMBSCREW: BRASS

**FINISH:**  
 THUMBSCREW: NICKEL PLATE

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005  ANGULAR TOLERANCES: ALL = ± 1°	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY C.MCCORMICK	01/28/2004			
	CHECKED BY D.PARHAM	01/28/2004	CATEGORY DATA CABLING		
	APPROVED BY R.CARRICK	01/28/2004	PRODUCT DESCRIPTION HD15 FEMALE WATERPROOF CONNECTOR		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. WPHDB15S-KIT	REV. <b>B</b>
		SCALE: NONE	CAD FILE: WPHDB15S-KIT.SLDDRW		SHEET 1 OF 1