USB Type A Female Panel Mount Coupler / 5 Meter Cable

Features for this product

- Allows USB cables to be passed through panels or enclosures
- Screw mount for secure installations
- 30 microinch gold plated contacts provide reliable connections with repeated mating cycles
- Cable is USB 2.0 compliant
- USB Type A panel mount female bulkhead connector with 5 meters of un-terminated USB cable





Another unique USB panel mount option allows the user the flexibility to configure their own assembly. It features a shielded bulkhead Type A Jack with 5 meters of un-terminated USB 2.0 compliant cable. The user can cut the cable to the desired length and hard wire or terminate it with their connector of choice. This assembly is fully shielded and uses the popular ECF style housing that is usable in virtually any panel thickness. L-com can custom terminate these cable ends with modest minimum requirements. Recommended 4-40 mounting screws must be purchased separately (P/N ECF440).

Details for this product

- otomo ror umo product		
L-com Item #	ECF504-5M	
Manufacturer	L-com	
UPC #	822335022300	
RoHS Status	RoHS Compliant 📀	

USB, Firewire, SCSI & Others > USB Couplers, Adapters and Covers



Item # Description Color

Panel Mounted USB Type Couplers, 30 Microinches Gold

These couplers are great for connecting USB style connectors into panels, etc. Available in many USB connector combinations with your choice of shielded and unshielded versions. Unshielded is available in Black or Ivory, shielded is Silver. Recommended 4-40 mounting screws must be purchased separately.

ECF504-UAB ECF504B-UAB	USB Type A - Type B Coupler USB Type A - Type B Coupler	lvory Black			
ECF504-UABS	USB Type A - Type B Coupler, Shielded	Silver			
ECF504-UAAS	USB Type A - Type A Coupler, Shielded	Silver			
ECF504-BAS	USB Type B - Type A Coupler, Shielded	Silver			
ECF440	Machine Screws, 4-40 x 5/16", Pkg/100				

USB Type A Female to Male Shielded Panel Mount Coupler, 30 Microinches Gold

This option features a bulkhead Type A jack to a molded Type A plug with USB 2.0 compliant cable. The assembly is fully shielded, 12 inches long and can be used in virtually any panel thickness. Recommended 4-40 mounting screws must be purchased separately.

ECF504-12AAS	USB Type A Coupler, Female Bulkhead / Male, 12 in	Silver
ECF440	Machine Screws, 4-40 x 5/16", Pkg/100	

USB Type A Female Panel Mount Coupler to 5 Meter Un-terminated Pigtail Cable


This addition to the popular USB panel mount adapter line allows users the flexibility to configure their own assembly. It features a shielded bulkhead Type A Jack with 5 meters of un-terminated USB 2.0 compliant cable. Users can cut the cable to the desired length and hard wire or terminate it with their connector of choice. (See page 105 for compatible USB Type A and B connectors). L-com can custom terminate these cable ends with modest minimum requirements. Recommended 4-40 mounting screws must be purchased separately.

ECF504-5M	JSB Type A Female Panel Mount Coupler / 5.0m Cable 11.95 11.74 11.29 10.59	
ECF440	Machine Screws, 4-40 x 5/16", Pkg/100	

USB Type A and B Panel Couplers with 10" Wire Leads, 30 Microinches Gold

Similar to our ECF504 USB coupler except with wire leads in the rear to connect to equipment. Choose from USB Type A or B jacks in Black or Ivory. Wires are 20 AWG (2 power) and 24 AWG (2 signal) stranded wires with an additional drain to shield. Recommended 4-40 mounting screws must be purchased separately.

ECJ504-UA ECJ504-UB	USB Type A Jack, 10" Leads USB Type B Jack, 10" Leads	lvory lvory			
ECJ504B-UA	USB Type A Jack, 10" Leads	Black			
ECJ504B-UB	USB Type B Jack, 10" Leads	Black			
ECF440	Machine Screws, 4-40 x 5/16", Pkg/100				



USB Adapters - Molded and Fully Shielded

These adapters provide an economical way for users to solve gender and connector type mismatches among standard USB connectors. They feature a durable fully molded design with internal shielding to protect signals from EMI/RFI interference.

Lt. Gray
Lt. Gray

USB Type A and B Connector Covers - Protect Unused Ports, Pkg/10

These covers are perfect for protecting unused female ports in our panel mount couplers or any expensive equipment from physical damage, dirt and dust. Made from soft ABS, these covers attach easily and stay in place with a snug friction fit. Color: Black.

CAPUSB-A	USB Protective Cover for Type A Jacks, Pkg/10	Black			
CAPUSB-B	USB Protective Cover for Type B Jacks, Pkg/10	Black			

CAPUSB-A