

	8		7		6		5 🔸	4		3	2		1
	THE INFORMATION PROPERTY OF L-CON WITHOUT THE WRITTE	A, INC. ANY REPRO	DUCTION IN F	PART OR WHOLE									
		PA RT NUMBER	COLOR	LENGTH FEET [METERS]	PA RT NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER	COLOR	LENGTH FEET [METERS]	PART NUMBER COLOR	LENGTH FEET [METERS]	
D		TRD815BLK-1	BLA CK	1 [0.31]	TRD815R-1	RED	1 [0.31]	TRD815OR-1	ORANGE	1 [0.31]	TRD815BL-1 BLUE	1 [0.31]	
		TRD815BLK-2	BLACK	2 [0.61]	TRD815R-2	RED	2 [0.61]	TRD815OR-2	ORANGE	2 [0.61]	TRD815BL-2 BLUE	2 [0.61]	
		TRD815BLK-3	BLACK	3 [0.91]	TRD815R-3	RED	3 [0.91]	TRD815OR-3	ORA NGE	3 [0.91]	TRD815BL-3 BLUE	3 [0.91]	4
		TRD815BLK-5	BLACK	5 [1.52]	TRD815R-5	RED	5 [1.52]	TRD815OR-5	ORANGE	5 [1.52]	TRD815BL-5 BLUE	5 [1.52]	4
		TRD815BLK-7	BLACK	7 [2.13]	TRD815R-7	RED	7 [2.13]	TRD8150R-7	ORA NGE	7 [2.13]	TRD815BL-7 BLUE	7 [2.13]	4
		TRD815BLK-10	BLACK	10 [3.05]	TRD815R-10	RED	10 [3.05]	TRD8150R-10	ORA NGE	10 [3.05]	TRD815BL-10 BLUE	10 [3.05]	-
		TRD815BLK-14	BLACK	14 [4.27]	TRD815R-14	RED	14 [4.27]	TRD8150R-14	ORA NGE	14 [4.27]	TRD815BL-14 BLUE	14 [4.27]	-
		TRD815BLK-20	BLACK	20 [6.10]	TRD815R-20	RED	20 [6.10]	TRD8150R-20	ORA NGE	20 [6.10]	TRD815BL-20 BLUE	20 [6.10]	-
		TRD815BLK-25	BLACK	25 [7.62]	TRD815R-25	RED	25 [7.62]	TRD8150R-25	ORA NGE	25 [7.62]	TRD815BL-25 BLUE	25 [7.62]	-
		TRD815BLK-30	BLACK	30 [9.14]	TRD815R-30	RED	30 [9.14]	TRD8150R-30	ORA NGE	30 [9.14]	TRD815BL-30 BLUE	30 [9.14]	-
		TRD815BLK-40	BLACK BLACK	40 [12.19]	TRD815R-40 TRD815R-50	RED	40 [12.19]	TRD8150R-40	ORA NGE	40 [12.19]	TRD815BL-40 BLUE TRD815BL-50 BLUE	40 [12.19]	-
		TRD815BLK-50 TRD815BLK-60		50 [15.24]	TRD815R-60	RED	50 [15.24] 60 [18.29]	TRD8150R-50 TRD8150R-60	ORA NGE ORA NGE	50 [15.24]	TRD815BL-50 BLUE TRD815BL-60 BLUE	50 [15.24]	
С		TRD815BLK-80	BLACK BLACK	60 [18.29] 75 [22.86]	TRD815R-60	RED	75 [22.86]	TRD8150R-66	ORA NGE ORA NGE	60 [18.29] 75 [22.86]	TRD815BL-75 BLUE	60 [18.29] 75 [22.86]	c
		TRD815BLK-80	BLACK	80 [24.38]	TRD815R-80	RED	80 [24.38]	TRD8150R-80	ORA NGE	80 [24.38]	TRD815BL-80 BLUE	80 [24.38]	- 1
		TRD815BLK-90	BLACK	90 [27.43]	TRD815R-90	RED	90 [27.43]	TRD8150R-90	ORA NGE	90 [27.43]	TRD815BL-90 BLUE	90 [27.43]	-
		TRD815BLK-100		100 [30.48]	TRD815R-100	RED		TRD8150R-100	ORA NGE	100 [30.48]	TRD815BL-100 BLUE	100 [30.48]	-
		TRD815GR-1	GREEN	1 [0.31]	TRD815Y-1	YELLOW	1 [0.31]	TRD815GRY-1	GRAY	1 [0.31]	TRD815V-1 VIOLET	1 [0.31]	-
		TRD815GR-2	GREEN	2 [0.61]	TRD815Y-2	YELLOW	2 [0.61]	TRD815GRY-2	GRAY	2 [0.61]	TRD815V-2 VIOLET	2 [0.61]	┫ │
•		TRD815GR-3	GREEN	3 [0.91]	TRD815Y-3	YELLOW	3 [0.91]	TRD815GRY-3	GRAY	3 [0.91]	TRD815V-3 VIOLET	3 [0.91]	-
-		TRD815GR-5	GREEN	5 [1.52]	TRD815Y-5	YELLOW	5 [1.52]	TRD815GRY-5	GRA Y	5 [1.52]	TRD815V-5 VIOLET	5 [1.52]	
		TRD815GR-7	GREEN	7 [2.13]	TRD815Y-7	YELLOW	7 [2.13]	TRD815GRY-7	GRA Y	7 [2.13]	TRD815V-7 VIOLET	7 [2.13]	1
		TRD815GR-10	GREEN	10 [3.05]	TRD815Y-10	YELLOW	10 [3.05]	TRD815GRY-10	GRA Y	10 [3.05]	TRD815V-10 VIOLET	10 [3.05]	
		TRD815GR-14	GREEN	14 [4.27]	TRD815Y-14	YELLOW	14 [4.27]	TRD815GRY-14	GRA Y	14 [4.27]	TRD815V-14 VIOLET	14 [4.27]	
		TRD815GR-20	GREEN	20 [6.10]	TRD815Y-20	YELLOW	20 [6.10]	TRD815GRY-20	GRA Y	20 [6.10]	TRD815V-20 VIOLET	20 [6.10]	
В		TRD815GR-25	GREEN	25 [7.62]	TRD815Y-25	YELLOW	25 [7.62]	TRD815GRY-25	GRA Y	25 [7.62]	TRD815V-25 VIOLET	25 [7.62]	В
_		TRD815GR-30	GREEN	30 [9.14]	TRD815Y-30	YELLOW	30 [9.14]	TRD815GRY-30	GRA Y	30 [9.14]	TRD815V-30 VIOLET	30 [9.14]	
		TRD815GR-40	GREEN	40 [12.19]	TRD815Y-40	YELLOW	40 [12.19]	TRD815GRY-40	GRA Y	40 [12.19]	TRD815V-40 VIOLET	40 [12.19]	1
		TRD815GR-50	GREEN	50 [15.24]	TRD815Y-50	YELLOW	50 [15.24]	TRD815GRY-50	GRA Y	50 [15.24]	TRD815V-50 VIOLET	50 [15.24]	1
		TRD815GR-60	GREEN	60 [18.29]	TRD815Y-60	YELLOW	60 [18.29]	TRD815GRY-60	GRA Y	60 [18.29]	TRD815V-60 VIOLET	60 [18.29]	1
		TRD815GR-75	GREEN	75 [22.86]	TRD815Y-75	YELLOW	75 [22.86]	TRD815GRY-75	GRA Y	75 [22.86]	TRD815V-75 VIOLET	75 [22.86]	1
		TRD815GR-80	GREEN	80 [24.38]	TRD815Y-80	YELLOW	80 [24.38]	TRD815GRY-80	GRA Y	80 [24.38]	TRD815V-80 VIOLET	80 [24.38]	
		TRD815GR-90	GREEN	90 [27.43]	TRD815Y-90	YELLOW	90 [27.43]	TRD815GRY-90	GRA Y	90 [27.43]	TRD815V-90 VIOLET	90 [27.43]	
		TRD815GR-100	GREEN	100 [30.48]	TRD815Y-100	YELLOW	100 [30.48]	TRD815GRY-100	GRA Y	100 [30.48]	TRD815V-100 VIOLET	100 [30.48]	
									·				CHWOOD DRIVE
												nnectivity	ANDOVER, MA 01845
A											CATEGORY	DULAR	A
											PRODUCT DESCRIPTION		
											CATEGORY	5E PATCH C	ORD
											SIZE FSCM NO. DWG. N 43321	o. TRD815-B	D REV.
											SCALE: NONE CAD FILE: TRD	815-B.SLDDRW	SHEET 2 OF 3
	8	I	7	I	6		5	4	I	3	2	I	1

	8	7	6	5	↓ 4	3	2	1	
-	THE INFORMATION CONTA PROPERTY OF L-COM, INC. WITHOUT THE WRITTEN PERM	AINED IN THIS DRAWING IS THE SOLI ANY REPRODUCTION IN PART OR WH MISSION OF L-COM, INC. IS PROHIBITED	OLE						
D									D
_			PART NUMBER COLOR	LENGTH					_
			TRD815WHT-1 WHITE TRD815WHT-2 WHITE	FEET [METERS] 1 [0.31] 2 [0.61]					
С			TRD815WHT-3 WHITE TRD815WHT-5 WHITE	3 [0.91] 5 [1.52]					С
			TRD815WHT-7 WHITE TRD815WHT-10 WHITE TRD815WHT-14 WHITE	7 [2.13] 10 [3.05] 14 [4.27]					
			TRD815WHT-20 WHITE TRD815WHT-25 WHITE	20 [6.10] 25 [7.62]					
-			TRD815WHT-30 WHITE TRD815WHT-40 WHITE TRD815WHT-50 WHITE	30 [9.14] 40 [12.19] 50 [15.24]					
			TRD815WHT-50 WHITE TRD815WHT-60 WHITE TRD815WHT-75 WHITE	50 [15.24] 60 [18.29] 75 [22.86]					
			TRD815WHT-80 WHITE TRD815WHT-90 WHITE TRD815WHT-100 WHITE	80 [24.38] 90 [27.43] 100 [30.48]					
В				100 [30.40]					В
_									
								obal 45 BEECHWOOD DRIVE NORTH ANDOVER, MA	E
А							CATEGORY	DDULAR	A
							PRODUCT DESCRIPTION	(5E PATCH CORD	
							SIZE FSCM NO. A 43321 DWG.	NO. RE	<u>▼.</u>
	8	7	6	5		3	SCALE: NONE CAD FILE: TRI		