IEEE-1394 Firewire Cable, Type 1 - Type 1, 1.0m

Features for this product


- Firewire cable assembly, Type 1 (6 position) to Type 1 connectors
- Simple plug and play connections avoid costly downtime
- Foil plus braid shield provides maximum protection against EMI/RFI
- Molded backshells provide durability and increased strength at cable entry point
- Lengths are 0.5, 1, 2, 3, & 5 meters; color is light gray



Highest quality firewire cables allow for transfer rates up to 400 Mbps and meet the IEEE-1394 specification. These cables allow for simple "plug & play" connections for devices such as printers, scanners, digital cameras and other firewire peripherals. They can also be used to link two computers together for file sharing. Twisted pair data lines help reduce crosstalk while 22 AWG power conductors enable maximum power transfer from host to peripheral. Quantity pricing available, please contact your L-com Sales Representative.

Details for this product			
L-com Item #	CSM94-1M		
Manufacturer	L-com		
UPC #	822335013902		
RoHS Status	<u>RoHS Compliant</u> 🤣		






Type 1 Connector



Type 2 Connector

108 USB, Firewire, SCSI & Others > IEEE-1394 Firewire Cable Assemblies



²⁰⁰⁰ Montor Potolog 4 0