RG59B Coaxial Cable, BNC Male / Male, 25.0 ft

Features for this product

- 75 Ohm video signal transmission
- True 75 Ohm BNC eliminates interface impedance mismatch
- RG59B/U solid center conductor minimizes insertion loss
- Crimp style attachment and molded strain relief result in a highly durable assembly
- Available from stock in 19 lengths ranging from .5 to 200 feet





When you need a well built, durable RG59B/U cable assembly with true 75 Ohm BNC male connectors and you need it now we have your cable assembly in stock. We offer these highly popular 75 Ohm coaxial cable assemblies with molded strain reliefs for maximum durability. In addition our true 75 Ohm BNC connectors feature gold plated center contacts for minimal attenuation and nickel plated bodies for enhanced corrosion resistance. We typically stock these cables in a multiple of standard lengths from .5 ft to 200 ft. We are sure to have just the length you are looking for in stock ready for immediate delivery.

Details for this Coaxial product							
L-com Item #	CC59B-25						
Manufacturer	L-com						
UPC #	822335006508						
RoHS Status	RoHS Compliant 📀						



Item #	Description				
RG59A/U	Ψ	Center Conductor: 22 (7x30) AWG bare	NON	AINAL ATTEN	UATION
		compacted copper	MHz	db/100 ft	db/100m
Ø.240 in. Nominal	Shielding: Bare copper braid (96% coverage)	50	2.1	6.9	
	Nominal	Insulation: Foam polyethylene	100	3.0	9.8
		Jacket: Black PVC	200	4.5	14.8
75.01	_ A	Operating Temperature: -40°C - +80°C	400	6.6	21.7
75 Ohm Impedance	e	Operating temperature: -40 C - +80 C	1000	10.9	35.8
DCEON/II 75 Ohm Coo	vial Cables	with Inline DNC to Type E Dlug			

RG59A/U - 75 Ohm Coaxial Cables with Inline BNC to Type F Plug CC59A-BF-1 RG59A Cable, BNC Male / Type F Male, 1.0 ft

CC59A-BF-3	RG59A Cable, BNC Male / Type F Male, 3.0 ft
CC59A-BF-6	RG59A Cable, BNC Male / Type F Male, 6.0 ft
CC59A-BF-9	RG59A Cable, BNC Male / Type F Male, 9.0 ft
CC59A-BF-12	RG59A Cable, BNC Male / Type F Male, 12.0 ft
RG59A/U - 7	75 Ohm Coaxial Cables with Two Type F Plugs
OCF59-1	RG59A Cable, Type F Male / Male, 1.0 ft
OCF59-3	RG59A Cable, Type F Male / Male, 3.0 ft
COEED 6	
CCF59-6	RG59A Cable, Type F Male / Male, 6.0 ft

RG59A Cable, Type F Male / Male, 100.0 ft RG59A/U - 75 Ohm Coaxial Cables with One Inline Type F Plug and One Type F Bulkhead Jack

RG59A Cable, Type F Male / Male, 12.0 ft RG59A Cable, Type F Male / Male, 25.0 ft RG59A Cable, Type F Male / Male, 50.0 ft

100010	TO CHILL COUNTER CADICO WITH CITO HIMIO TYPE
CCF59-MF-1	RG59A Cable, Type F Male / Female, 1.0 ft
CCF59-MF-6	RG59A Cable, Type F Male / Female, 6.0 ft
CCF59-MF-12	RG59A Cable, Type F Male / Female, 12.0 ft
CCF59-MF-25	RG59A Cable, Type F Male / Female, 25.0 ft
CCF59-MF-50	RG59A Cable, Type F Male / Female, 50.0 ft

RG59A/U - 75 Ohm Coaxial Cables with Two Inline RCA Plugs

nussevu - 15	Offili Coaxial Cables with two filling in
CC59A-RR-1	RG59A Cable, RCA Male / Male, 1.0 ft
CC59A-RR-3	RG59A Cable, RCA Male / Male, 3.0 ft
CC59A-RR-6	RG59A Cable, RCA Male / Male, 6.0 ft
CC59A-RR-9	RG59A Cable, RCA Male / Male, 9.0 ft
CC59A-RR-12	RG59A Cable, RCA Male / Male, 12.0 ft

RG59A/U - 75 Ohm Coaxial Cables with Inline RCA to Inline BNC Plug

CC59A-RB-1	RG59A Cable, RCA Male / BNC Male, 1.0 ft
CC59A-RB-3	RG59A Cable, RCA Male / BNC Male, 3.0 ft
CC59A-RB-6	RG59A Cable, RCA Male / BNC Male, 6.0 ft
CC59A-RB-9	RG59A Cable, RCA Male / BNC Male, 9.0 ft
CC59A-RB-12	RG59A Cable, RCA Male / RNC Male, 12.0 ft

RG59A/U - 75 Ohm Coaxial Cables with Inline RCA to Type F Plug

OC59A-RF-1	RG59A Cable, RCA Male / Type F Male, 1.0 ft
CC59A-RF-3	RG59A Cable, RCA Male / Type F Male, 3.0 ft
CC59A-RF-6	RG59A Cable, RCA Male / Type F Male, 6.0 ft
CC59A-RF-9	RG59A Cable, RCA Male / Type F Male, 9.0 ft
CC59A-RF-12	RG59A Cable, RCA Male / Type F Male, 12.0 ft

RG59B/U - 75 Ohm Coaxial Cables with Molded BNC Plugs

L-com offers a wide variety of RG59B/U cable assemblies utilizing BNC and Type F connectors. RG59B/U cable is one of the most commonly used 75 Ohm cables. In addition to inline configurations L-com offers right angle and female bulkheads. All connectors feature a molded strain relief while the Type F connector features a captivated gold plated center pin for enhanced performance. The solid center conductor of the RG59B/U cable provides optimum insertion loss performance.

RG59B/U ₩	Center Conductor: 22 AWG solid bare copper		NOMINAL ATTENUATION			
	covered steel	MHz	db/100 ft	db/100m		
Ø.242 in.	 Shielding: Bare copper braid (95% coverage) 	50	2.4	7.9		
Nominal	Insulation: Polyethylene	100	3.4	11.1		
	Jacket: Black PVC	200	4.9	16.1		
75 Ohm Impodonso	• Operating Temperature: -40°C - +80°C	400	7.0	23.0		
75 Ohm Impedance	Operating remperature: -40 C - +60 C	1000	12.0	39.3		

RG59B/U - 75 Ohm Coaxial Cables with Two Inline BNC Plugs

CC59B-05	RG59B Cable, BNC Male / Male, 0.5 ft
CC59B-1	RG59B Cable, BNC Male / Male, 1.0 ft
CC59B-1.5	RG59B Cable, BNC Male / Male, 1.5 ft
CC59B-2	RG59B Cable, BNC Male / Male, 2.0 ft
CC59B-2.5	RG59B Cable, BNC Male / Male, 2.5 ft
CC59B-3	RG59B Cable, BNC Male / Male, 3.0 ft
CC59B-4	RG59B Cable, BNC Male / Male, 4.0 ft
CC59B-5	RG59B Cable, BNC Male / Male, 5.0 ft
CC59B-6	RG59B Cable, BNC Male / Male, 6.0 ft
CC59B-7.5	RG59B Cable, BNC Male / Male, 7.5 ft
CC59B-10	RG59B Cable, BNC Male / Male, 10.0 ft
CC59B-12	RG59B Cable, BNC Male / Male, 12.0 ft
CC59B-15	RG59B Cable, BNC Male / Male, 15.0 ft
CC59B-25	RG59B Cable, BNC Male / Male, 25.0 ft
CC59B-50	RG59B Cable, BNC Male / Male, 50.0 ft
CC59B-75	RG59B Cable, BNC Male / Male, 75.0 ft
CC59B-100	RG59B Cable, BNC Male / Male, 100.0 ft
CC59B-150	RG59B Cable, BNC Male / Male, 150.0 ft
CC59B-200	RG59B Cable, BNC Male / Male, 200.0 ft
	,

