# Molded S-Video Cable, Male / Male, 2.0 ft

### Features for this product


- Length of cable 2 feet
- Dual coaxial cables support high quality video signal transmission
- Gold plated contacts reduce signal loss
- Molded strain reliefs produce a durable cable assembly
- Available from stock in 10 lengths ranging from 1 to 50 feet




These high quality S-Video cable assemblies utilize dual 75 Ohm coaxial cables for unmatched video signal transmission. The molded strain relief Mini Din 4 male connectors with gold plated contacts assure distortion free performance. We typically carry these exceptional quality cable assemblies in stock in 10 handy lengths from 1 to 50 ft.

Details for this Monitor, Video product				
L-com Item #	CCD234MM-2			
Manufacturer	L-com			
UPC #	822335007000			
RoHS Status	Not Compliant At This Time			

## Monitor / Video > S-Video (SVHS) Cable Assemblies 92





~		00000			,				-
<u>MM-1</u>			Molded	Mini	DIN 4	Male	/ Male,	1.0 ft	
<u>MM-2</u>			Molded	Mini	DIN 4	Male	/ Male,	2.0 ft	
<u>MM-3</u>			Molded	Mini	DIN 4	Male	/ Male,	3.0 ft	
<u>MM-5</u>			Molded	Mini	DIN 4	Male	/ Male,	5.0 ft	
MM-7	.5		Molded	Mini	DIN 4	Male	/ Male,	7.5 ft	
MM-1	0		Molded	Mini	DIN 4	Male	/ Male,	10.0 ft	
MM-2	0		Molded	Mini	DIN 4	Male	/ Male,	20.0 ft	
MM-3	0		Molded	Mini	DIN 4	Male	/ Male,	30.0 ft	
MM-4	0		Molded	Mini	DIN 4	Male	/ Male,	40.0 ft	
MM-5	0		Molded	Mini	din 4	Male	/ Male,	50.0 ft	
MF-1			Molded	Mini	DIN 4	Male	/ Femal	le, 1.0 ft	
MF-2			Molded	Mini	DIN 4	Male	/ Femal	le, 2.0 ft	
MF-3			Molded	Mini	DIN 4	Male	/ Femal	le, 3.0 ft	
MF-5			Molded	Mini	DIN 4	Male	/ Femal	le, 5.0 ft	
MF-7.	5		Molded	Mini	DIN 4	Male	/ Femal	le, 7.5 ft	
MF-10	2		Molded	Mini	DIN 4	Male	/ Femal	le, 10.0 f	ft
MF-20	2		Molded	Mini	din 4	Male	/ Femal	le, 20.0 1	ft
bla		daa Ca			mbl	ine	75.0	hm D	

	1400	
<u>IM-1</u>		Assembled Mini DIN 4 Male / Male, 1.0 ft
<u>1M-2</u>		Assembled Mini DIN 4 Male / Male, 2.0 ft
<u>1M-3</u>		Assembled Mini DIN 4 Male / Male, 3.0 ft
<u>1M-5</u>		Assembled Mini DIN 4 Male / Male, 5.0 ft
<u>1M-7.5</u>		Assembled Mini DIN 4 Male / Male, 7.5 ft
<u>1M-10</u>		Assembled Mini DIN 4 Male / Male, 10.0 ft
1M-20		Assembled Mini DIN 4 Male / Male, 20.0 ft
<u>1F-1</u>		Assembled Mini DIN 4 Male / Female, 1.0 ft
1F-2		Assembled Mini DIN 4 Male / Female, 2.0 ft
1F-3		Assembled Mini DIN 4 Male / Female, 3.0 ft
<u>1F-5</u>		Assembled Mini DIN 4 Male / Female, 5.0 ft
4F-7.5		Assembled Mini DIN 4 Male / Female, 7.5 ft
/F-10		Assembled Mini DIN 4 Male / Female, 10.0
<u> 1F-20</u>		Assembled Mini DIN 4 Male / Female, 20.0