

HyperLink Wireless 900 MHz 8 dBi Flat Patch Antenna Model: HG908P

Applications

- 900 MHz ISM band
- Wireless LAN systems
- GSM, RFID and SCADA
- Wireless video links
- 900 MHz cellular

Features

- Durable UV-stable, UL flame rated radome
- Light weight and only 8.5 inches square
- Low loss solid brass elements
- Can be installed for either vertical or horizontal polarization
- Optional mounting kits available

Description

Only 8.5 inches square!

This high gain flat patch antenna provides 8 dBi gain with broad coverage. It is suitable for both indoor and outdoor wireless LAN and wireless video applications in the 900MHz ISM band, GSM, 900MHz cellular and RFID applications.

Rugged and Weatherproof

This antenna's construction features sealed internal elements and an aesthetic UV-stable, UL flame rated white plastic radome. Can be wall or mast mounted using U-bolts.

Custom Connectors

Custom Connectors are available for this antenna.

Specifications

Mechanical Specifications

Frequency	902-928 MHz
Gain	8 dBi
Horizontal Beam Width	75 Degrees
Vertical Beam Width	65 Degrees
Impedance	50 Ohm
VSWR	< 1.5:1 avg.








Electrical Specifications

Weight	< 1 lbs. (0.45 kg)	
Dimensions	8.5 x 8.5 x 1.2 in (215.9 x 215.9 x 30.4 mm)	
Radome Material	UV-inhibited Polymer	
Flame Rating	UL 94HB	
Mounting	Four ¼" Holes	
Polarization	Horizontal or Vertical	
Operating Temperature	-40°C to 85°C (-40°F to 185°F)	
Wind Survival	>150 MPH	
RoHS Compliant	Yes	

Wind Loading Data

Wind Speed (MPH)	Loading (lbs)
100	16
125	26

RF Antenna Gain Patterns





Mounting Options

Hyperlink's patch antennas offer several unique mounting options. They can be mounted flat against a wall, or to a mast using a pair of 2 inch U-bolts. The antennas also accept most tilt-and-swivel security camera brackets equipped with standard 1/4-20 threads.

	Description	Part Number
	Small Metal Tilt-and-Swivel Mounting Bracket for indoor wall mounting. Includes wall-mounting hardware.	HGX-PMT02
	Medium Plastic Tilt-and-Swivel Mounting Bracket for indoor wall mounting. Includes wall-mounting hardware.	HGX-PMT03
R A	Large Metal Tilt-and-Swivel Mounting Bracket for indoor and outdoor wall or mast mounting. Includes wall-mounting hardware. Can be mast-mounted using U-Bolt Kit (sold separately).	HGX-PMT04
2	Universal Antenna Mount powder coated galvanized steel "DSS-style" arm for outdoor wall mounting. Requires a pair of 2 inch U-bolts (sold separately).	HGX-UMOUNT
*	Stationary Mounting Kit for mounting to 1-1/4" to 2" dia. masts. Includes U-Bolts, nuts and mast clamp.	HGX-PMT07
C.	60 Degree Tilt-and-Swivel Mounting Kit for mounting to 1-1/4" to 2" dia. masts. Mounting hardware included.	HGX-PMT06
	Ceiling/Wall Universal Antenna Mount can be used with 4.5" sq and 8.5" sq. patch antennas as well as N-Type bulkhead and TNC/BNC bulkhead omni directional antennas. Includes ceiling/wall mounting hardware.	
	Universal Corner Mounting Bracket: This bracket is designed to mount to an outside corner of a structure. It can be used with 4.5" and 8.5" sq. patch antennas, radome enclosed Yagi antennas, the HGX-PMT02 tilt & swivel bracket and can accommodate the SC2402N and SC5802N 2-Way signal splitters as well as HyperAmp outdoor amplifiers.	HGX-UMOUNT03
	Window Mounting Kit Includes suction cups and mounting hardware.	HGX-PMT08