

## Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 15.0 ft

Features for this Telecom/Modular product

- Category 5E rated for High Speed Network Performance
- Aluminized Polyester Shield for protection from EMI
- EIA568 Compliant for compatibility with your network
- 26AWG stranded conductors for flexibility
- Available in lengths from 2 Ft to 100 Ft








**For Protection against EMI/RFI interference L-com's economical Shielded Patch Cables are ideal. With a 100% foil shield covering 4-Pair 26AWG stranded conductors, your data is protected from interference. This series is designed to perform to EIA568 standards while not putting a strain on your budget. Quantity pricing available upon request.**

Details for this product

L-com Item #	TRD855SCR-15
Manufacturer	L-com
UPC # (More)	822335037892
RoHS Status	<a href="#">RoHS Compliant</a>  (More)
Color	Lt.Gray

Applications for this Telecom/Modular product

- Industrial Ethernet
- 10/100BASE-TX
- Factory Automation
- Process Industry applications
- Harsh Environment applications

-  [Diagram](#)
-  [Catalog Page](#)
-  [Catalog Page](#)
-  [2D Drawing \(.pdf\)](#)
-  [3D CAD Model \(.step\)](#)

Similar Products In Stock