



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|---------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 3/23/11 | D.GRIFFIN |
| | | | |
| | | | |




RJ45 (8X8) FEMALE
SHIELDED CONNECTOR



ABS
(BLACK)



RJ45 (8X8) FEMALE
SHIELDED CONNECTOR



NOTES:

1. INGRESS PROTECTION RATING IP67
2. COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.

RoHS Compliant ✓

| | | | | | |
|---|--|-------------------------|---|--------------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ±.005 | APPROVALS | DATE |  Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | | |
| | DRAWN BY D. CASTRO | 3/23/11 | | | |
| | CHECKED BY D. PARHAM | 3/23/11 | CATEGORY | MODULAR | |
| | APPROVED BY J. RUST | 3/23/11 | | | |
| PROJECTION  | CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | | PRODUCT DESCRIPTION | | |
| | | | ENET FR/FR PASS-THRU SHLD | | |
| | SIZE | FSCM NO. | DWG. NO. | REV. | |
| | A | 43321 | WJP1F5 | A | |
| SCALE: NONE | | CAD FILE: WJP1F5.SLDDRW | | SHEET 1 OF 1 | |