


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


RoHS Compliant ✓

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
F	ECN 3690: CN RELEASE	29.Oct.2008	Bill_Zhang
G	ECN4146: CAP MATERIAL WAS PVC. UPDATED FORMAT.	07/22/09	D.FP
H	ECN 4320: ADDED NOTE 3 & 4, ADDED 2X .91 DIM	10/20/09	D. CASTRO
J	ECN 5837: ADDED LOGO	11/16/11	D. CASTRO

PART NUMBER	LENGTH FEET (METER)
CTLDVI-HD-MM-3	3.0 (0.92)
CTLDVI-HD-MM-5	5.0 (1.52)
CTLDVI-HD-MM-10	10.0 (3.05)
CTLDVI-HD-MM-15	15.0 (4.57)



WIRING MAP



NOTES:

1. CABLES TO BE TESTED FOR CONTINUITY
2. CABLES TO BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY Bill_Zhang	10/29/08	
	CHECKED BY Frank_Mao	10/29/08	CATEGORY
	APPROVED BY Thomas_Lu	10/29/08	VIDEO
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION	
COLOR VARIATIONS MAY OCCUR		DVI-A M/HD15P M W/FERRITE	
REF	SIZE A	FSCM NO. 43321	DWG. NO. CTLDVI-HD-MM
SCALE: NONE		CAD FILE: CTLDVI-HD-MM.SLDDRW	REV. J
SHEET 1 OF 1			