


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 4474: ADDED 1.0 FT. LENGTH, UPDATED FORMAT, ADDED NOTES	1/7/10	D. CASTRO
-	-	-	-
-	-	-	-
-	-	-	-



"P1"  
15-PIN MALE  
D-SUB CONNECTOR  
GOLD PLATED PINS

"J1"  
15 CONTACT FEMALE  
D-SUB CONNECTOR  
GOLD PLATED CONTACTS

WIRING MAP		
"P1"	WIRE COLOR	"J1"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK / WHITE	13
14	BROWN / WHITE	14
15	RED / WHITE	15
SHELL	DRAIN WIRE	SHELL

PART NUMBER	LENGTH	
	FEET	METERS
CSMN15MF-1	1	0.31
CSMN15MF-2.5	2.5	0.76
CSMN15MF-5	5	1.52
CSMN15MF-10	10	3.05
CSMN15MF-15	15	4.57
CSMN15MF-25	25	7.62
CSMN15MF-50	50	15.24

**RoHS Compliant** ✓

- NOTES:**
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
  - CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM PACKAGING SPEC. PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY TJC	6/6/01		CHECKED BY DFP	7/18/01
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY <b>DATA CABLING</b>		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>CSMN15MF</b>	
CSMN-FS01		SCALE: NONE	CAD FILE: CSMN15MF.SLDRW	SHEET 1 OF 1	

45 BEECHWOOD DRIVE  
NORTH ANDOVER, MA  
01845

CATEGORY  
**DATA CABLING**

PRODUCT DESCRIPTION  
**DELUXE MOLDED CABLE, DB15M TO DB15F**

SIZE **A** FSCM NO. **43321** DWG. NO. **CSMN15MF** REV. **E**

SCALE: NONE CAD FILE: CSMN15MF.SLDRW SHEET 1 OF 1