

Right Angle - 2 Leads Clear Epoxy - 30 deg Angle

INDEX

PRODUCT TREE



SPEC! Image next to part no. indicates cad file.

- [Product Table](#)
- [Table Footnotes](#)
- [Order Samples](#)
- [Stock/Price Request](#)
- [Sales and Tech Support](#)

1. [Product Gallery](#)
2. [Opto-Electronic Components](#)
3. [Phototransistors](#)
4. [Side Sensing/Right Angle Phototransistors](#)
5. [Right Angle - 2 Leads Clear Epoxy - 30 deg Angle](#)

Lumex drawings are in PDF format. If you don't have Adobe Acrobat, click on this icon to

[download a free copy](#)



Lumex Part Number	Lens	Vceo (V) Max *	PC (mW) Max *	t-opr (deg C) *	Iceo @ 10 Vceo (nA) Max	Ic (mA) Min **	Ic (mA) Typ **	Ic (mA) Max **	Vce (V) **	lambda p (nm) Typ.	delta theta deg Typ.	lambda (nm)	tr/ta @ Vec 5V Ic 1ma
OED-ST-1556SN SPEC!	Clear Epoxy	30	100	- 40 ; + 85	100	-	6	-	5	900	+/- 15	600 ; 1050	15/15 mS

Table Footnotes

[\[top of page\]](#)

- * Limits of Safe Operation
- ** @ EV ~ 1000 Lx

[Home](#) |
 [What's New](#) |
 [Product Gallery](#) |
 [Product Search](#) |
 [X-Ref Search Engine](#) |
 [Tech Notes](#) |
 [Sales and Tech Support](#) |
 [Corporate Info](#)

[com](#)

© 1997-2001 Lumex, Inc.