



DR100 INLET

31-68177-K07

SPECIFICATIONS

100 A

125/250 VAC

Type 4X & IP69

Rated Current (A)	100 A
Rated Voltage (V)	125/250 VAC
Contact Configuration	3P+N+G
Auxiliary Contacts	NO AUX
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	10 AWG - 2 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	4
Base Drawing Number	31-68xxx-kxx.PDF
Catalog	meltric-catalog-dr100-en.pdf