



# PN12c INLET

03-A8001

## SPECIFICATIONS

2 A/7.5 A

600 VAC/130 VDC

IP66/IP67

<b>Rated Current (A)</b>	2 A/7.5 A
<b>Rated Voltage (V)</b>	600 VAC/130 VDC
<b>Contact Configuration</b>	11P+G
<b>Ratings Information</b>	CURRENT INTERRUPTING
<b>Environmental Rating</b>	IP 66/67
<b>Impact Rating</b>	IK09
<b>Material</b>	POLY
<b>Product Color</b>	BLUE
<b>Minimum Operating Temperature</b>	-40F -40C
<b>Maximum Operating Temperature</b>	140F 60C
<b>Wiring Capacity - Phase Contacts</b>	18 AWG - 14 AWG SOLDER/CRIMP TERMINAL
<b>Accessory Size</b>	1
<b>Base Drawing Number</b>	<a href="#">03-a8001.pdf</a>
<b>Catalog</b>	<a href="#">meltric-catalog-pn12c-en.pdf</a>