


Rev	AWO #	Description	Date	Appr
-		RELEASED	06/07/12	

APPROVED: _____

DATE: _____ TITLE: _____



WASHER	BRASS	NICKEL
DIELECTRIC	DELRIN	NONE
PIN	BRASS	GOLD
BODY	BRASS	NICKEL
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohm
 Frequency range: 0-4 GHz
 Working Voltage: 500 VRMS Max.
 VSWR: 1.3 max. (Straight)
 1.5 max. (Right Angle)

Contact Resistance: 3 Milliohms max. (Center Contact)
 2 Milliohms max. (Outer Contact)

Insulator Resistance: 5,000 Megohms min.

Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE MM [INCHES]
 TOLERANCES: EXCEPT AS NOTED
 INCHES

.X	$\pm .10$	ϕX	$\pm .10$
.XX	$\pm .020$	ϕXX	$\pm .015$
.XXX	$\pm .015$	ϕXXX	$\pm .010$

APPROVALS	DATE
DRAWN TW	06/07/12
CHECKED AY	06/07/12
APPROVED	

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

BNC JACK ADAPTOR, 50 OHMS

SIZE	PART NO.	REV.
X	RF1-99-D-AS-50	-
REF:	S00049T	SCALE: NTS
		SHEET 1 OF 1