



DS100 INLET

37-98043

SPECIFICATIONS

100 A
 480 VAC
 Type 4X & IP69
 30 hp

Rated Current (A)	100 A
Rated Voltage (V)	480 VAC
Horsepower Rating	30 hp
Contact Configuration	3P+G
Auxiliary Contacts	NO AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK10
Material	METAL
Metal Type	ALUMINUM
Product Color	METAL
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	4 AWG - 2/0 AWG SCREW TERMINAL
Applicable Standards	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	5
Base Drawing Number	37-98xxx.PDF
Catalog	meltric-catalog-ds100-en.pdf