



DS30 INLET

33-38043

SPECIFICATIONS

30 A
 480 VAC
 Type 3R
 15 hp

Rated Current (A)	30 A
Rated Voltage (V)	480 VAC
Horsepower Rating	15 hp
Contact Configuration	3P+G
Auxiliary Contacts	NO AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 3R IP 54
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG - 4 AWG SCREW TERMINAL
Applicable Standards	UL 2682 UL 1682 cCSAus C22.2 No. 182.1-13
Accessory Size	3
Base Drawing Number	33-38xxx.PDF
Catalog	meltric-catalog-ds30-en.pdf