



DR150 RECEPTACLE

31-94243-K04-843

SPECIFICATIONS

150 A
 480 VAC
 Type 4X

Rated Current (A)	150 A
Rated Voltage (V)	480 VAC
Contact Configuration	3P+G
Auxiliary Contacts	NO AUX
Ratings Information	NON-CURRENT INTERRUPTING
Environmental Rating	Type 4X IP 66/67
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	4 AWG - 2/0 AWG SCREW TERMINAL
Applicable Standards	UL 1682 cCSAus C22.2 No. 182.1-13
Option(1)	PADLOCK PAWL
Accessory Size	5
Base Drawing Number	31-94xxx-kxx.PDF
Catalog	meltric-catalog-dr150-en.pdf