





Rev	AWO #	Description	Date	Appr
-		RELEASED	4/6/05	

APPROVED: _____
 DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

G = Gold flash over Nickel underplate overall
 T = Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating: -55°C to +105°C

Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES [MM]
 .X ± .10 ØX ± .10
 .XX ± .020 ØXX ± .015
 .XXX ± .015 ØXXX ± .010

ADAM TECH
 909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

DRAWN	SS	4/6/05
CHECKED		
APPROVED		

TITLE	.200 [5.08] MINI SHUNT, CLOSED TOP	
SIZE	PART NO.	MSE-X
REF:	SCALE:	NTS
SHEET	1	OF 1

