



DSN24c INLET

63-B8002

SPECIFICATIONS

2 A/7.5 A

480 VAC/130 VDC

IP66/IP67

Rated Current (A)	2 A/7.5 A
Rated Voltage (V)	480 VAC/130 VDC
Contact Configuration	23P+G
Ratings Information	CURRENT INTERRUPTING
Environmental Rating	IP 66/67
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	18 AWG – 14 AWG SOLDER/CRIMP TERMINAL
Accessory Size	2
Base Drawing Number	63-b8002.pdf
Catalog	meltric-catalog-dsn24c-ds24c-en.pdf