



DSN30 INLET

63-38043-972

SPECIFICATIONS

30 A

480 VAC

Type 4X & IP69

15 hp

Rated Current (A)	30 A
Rated Voltage (V)	480 VAC
Horsepower Rating	15 hp
Contact Configuration	3P+G
Auxiliary Contacts	+2 AUX
Ratings Information	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
Environmental Rating	Type 4X IP 66/67 IP 69
Short Circuit Rating	100 kA - CLOSE & WITHSTAND
Impact Rating	IK09
Material	POLY
Product Color	BLUE
Minimum Operating Temperature	-40F -40C
Maximum Operating Temperature	140F 60C
Wiring Capacity - Phase Contacts	14 AWG - 8 AWG SCREW TERMINAL
Applicable Standards	UL 1682 UL 2682 cCSAus C22.2 No. 182.1-13
Accessory Size	2
Base Drawing Number	63-38xxx.PDF
Catalog	meltric-catalog-dsn30-en.pdf