



# DSN60 RECEPTACLE

63-64072-375

## SPECIFICATIONS

60 A

250 VAC

Type 4X & IP69

3 hp

<b>Rated Current (A)</b>	60 A
<b>Rated Voltage (V)</b>	250 VAC
<b>Horsepower Rating</b>	3 hp
<b>Contact Configuration</b>	2P+G
<b>Auxiliary Contacts</b>	NO AUX
<b>Ratings Information</b>	SWITCH RATED BRANCH CIRCUIT DISCONNECT SWITCH MOTOR CIRCUIT DISCONNECT SWITCH
<b>Environmental Rating</b>	Type 4X IP 66/67 IP 69
<b>Short Circuit Rating</b>	100 kA - CLOSE & WITHSTAND
<b>Impact Rating</b>	IK09
<b>Material</b>	POLY
<b>Product Color</b>	BLUE
<b>Minimum Operating Temperature</b>	-40F -40C
<b>Maximum Operating Temperature</b>	140F 60C
<b>Wiring Capacity - Phase Contacts</b>	14 AWG - 4 AWG SCREW TERMINAL
<b>Applicable Standards</b>	UL 1682 UL 2682 cCSAus C22.2 No. 182.1-13
<b>Option(1)</b>	MUSHROOM PAWL
<b>Accessory Size</b>	3
<b>Base Drawing Number</b>	<a href="#">63-64xxx.pdf</a>
<b>Catalog</b>	<a href="#">meltric-catalog-dsn60-en.pdf</a>