

## FWZ Series FWZ72-BlackPolycarbonate

FWZ 36, 53, and 55 Hour Meters are rectangular flush panel mount designed to fit into tight locations. All can withstand IP54

environmental rating (requires use of gasket).



## Specifications:

• Bezel: 2.83" round (72mm) 3-hole

• Capacity: 99.999.99 hours

• Digits: 7 – 0.16" high numerals

• Voltage: 24, 120, 240, 50 or 60Hz models

• Power Consumption: 1VA

• Temperature: -40° to 160°F (-40° to 72°C)

• Termination: Combination 1/4" spade and screw clamp.

Rear access

screw terminals available (model "K")

• Weight: 1.8oz

• Flush panel mounted with (3) 0.185" holes for #8 screws

• Panel Opening: 1.75" round (44.5mm) or 1.50" x 1.00"

rectangular (38 x 25mm)