

## UWZ Series UWZ48EFlushMount

The UWZ 48 Series is designed to meet IP20 environmental rating for

indoor applications. All models are light grey color with white

numerals on black background. Tenths and hundredths numerals are

yellow. An orange dial adjacent to the hundredths digit provides running indication.



## **Specifications**

• Bezel: 1.89" x 1.89" (48 x 48mm)

• Capacity: 99,999.99 hours

Mounting: SurfaceDigits: 7 – 0.16" high

• Voltage: 24, 120, 240, 50 or 60Hz

• Power Consumption: 1VA

• Temperature: -40° to 160°F (-40° to 72°C)

• Termination: Screw Lugs

• Weight: 2.1oz.

• Surface mounted type.

 Flush mounted with bracket. The UWZ 48E unit fits into a 1.79 x

1.79in. (45.5  $\times$  45.5mm) cut-out. The thickness of the panel for flush

mounting can be up to 0.35in. (9mm). The unit is secured in position by

a plastic slip-on retaining bracket. Also fits square or round openings

for 72mm meters with optional 72mm bezel.