
THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION						
REV.	DESCRIPTION	DATE	APPROVED			
В	RoHS Compliancy	06-01-06	DP			

	51.3
65.0	
	Ø7.6ID
	→   <sub>Ø13.0</sub>   →



## NOTES:

## MATERIAL:

MOULDING: NYLON, FLAMMABILITY RATING U.L. 94V-0

CONTACTS: BRASS, NICKEL PLATED

RATING: 10A 250V AC

INSULATION RESISTANCE: >1000 M OHM CONTACT RESISTANCE: < 10m OHM

A.C. BREAKDOWN: POLE-POLE: 4.5kV POLE-ACCESSIBLE: 4kV

OPERATING TEMPERATURE: -40° C TO +70° C WITHDRAWL FORCE: 10N (MIN), 50N (MAX)

APPROVALS: UL,CSA,VDE

FOR USE WITH 18 AWG CORDAGE

**RoHS COMPLIANT** 

## CONTROLLED

Dim range	Tolerance +/-	Qualtek Electronics Corp.  PPC DIVISION		
(mm)	(mm)	Part Number:	705-00/00	RoHS Compliant
0-1	0.15	Description: REWIRABLE PLUG ASSEMBLY		
1-6	0.20			
6-18	0.30			DE1 / D
18-50	0.50		UNIT: mm	REV. B
50-120	0.70	Drawn / Date	Checked / Date	Approved / Date
120-250	0.90	B.Zhang	12-30-02	JJH / 12-30-02
250-500	1.20	12-30-02		