
# XTRA•GUARD® 4 EXTRA-PROTECTION, HIGH/LOW TEMPERATURE TPE JACKET

## NOW CSA AWM I A/B II A/B FT1 CERTIFIED!

Specify XTRA•GUARD® 4 for unmatched cable performance in both high and low temperature cable applications from -60°C to 125°C. XTRA•GUARD® 4 has outstanding resistance to oils, fuels, solvents, water, low HCL content for safety and passes the 210,000<sup>++</sup> BTU Flame Test. XTRA•GUARD® 4 features fully color-coded TPE (Thermoplastic Elastomer) insulated conductors and a TPE jacket in both 300 Volt and 600 Volt UL cable styles. XTRA•GUARD® 4 is CSA Certified and UL Rated Type TC 600 Volt and Type PLTC 300 Volt for cable tray applications and is Pennsylvania Bureau Deep Mine Safety Approved (P-MWMS-1-85) for mine-wide monitoring systems.

## **APPLICATIONS**

- Wood, Paper, Pulp, Plant Operations
- Mining Instruments and Controls
- Mass Transit Systems
- Military Electronic Applications
- Food and Beverage Plants
- Petrochemical Process Controls
- Arctic Pipeline Controls



TUBING RECOMMENDATION
TO-600 – Highly Flexible, Irradiated Elastomer (See Page 131 for Product Specifications)
To-400 – Temperature/Chemical Resistant FEP Teflon®
(See Page 129 for Product Specifications)



Teflon® is a registered trademark of E.I. DuPont Co.





UL TYPE PLTC
UL AWM STYLE 20237
CSA AWM I A/B II A/B FT1
RoHS COMPLIANT
300 VOLT

# XTRA·GUARD® 4

## **MULTIPAIR, SUPRASHIELD®**

### EXTRA-PROTECTION, HIGH/LOW TEMPERATURE TPE JACKET

## **CHOOSE XTRA-GUARD 4 For:**

- Three Times the Low-Temperature Flexibility of Conventional PVC
- Unmatched Performance at Temperatures from -40°C to 125°C
- Resistance to Oils, Fuels, Solvents and Water
- UL Recognition, UL Listing and CSA Certification
- Unmatched Flame Resistant Insulation and Jacket
- Ultraviolet Light Stability (jacket color black)
- SUPRASHIELD Twice as Effective as Foil Shielding

## **XTRA**·GUARD 4 APPLICATIONS:

- Wood, Paper, Pulp, Plant Operations
- Mining Instruments and Controls
- Mass Transit Systems
- Food and Beverage Plants
- Petrochemical Process Controls
- Arctic Pipeline Controls

## **CHARACTERISTICS**

#### **OPERATING TEMPERATURE:**

■ -40°C to 125°C

#### **VOLTAGE RATING:**

■ 300 Volt

#### **COLOR DESCRIPTION:**

- Color Code: Chart B Page 374
- Jacket Colors: Yellow, Örange, Blue, Green, Red, Black, White and Gray

#### PRODUCT DESCRIPTION:

- Conductor: Stranded Tinned Copper
- Insulation: Color-Coded Thermoplastic Elastomer
- SUPRASHIELD: Aluminum/Polyester/Aluminum Foil with Stranded Tinned Copper Drain Wire Equal in Size to Insulated Conductors of Cable plus 70% Overall Braid of Tinned Copper
- Nylon Rip Cord for Ease of Jacket Stripping
- Jacket: Thermoplastic Elastomer

## **SPECIFICATIONS**

- UL AWM Style 20237
- UL Type PLTC
- CSA AWM I A/B II A/B FT1
- Passes 210,000 BTU Flame Test
- Pennsylvania Bureau of Deep Mine Safety Approved P-MWMS-1-85
- RoHS Compliant









## **AVAILABILITY**

- ▲ In Stock: 500 ft (152m) and 1000 ft (305m) put-ups, check for jacket color availability
- Made-To-Order: All available jacket colors, 1,000 ft (305m) minimum

August Au

20 AWG (0,56mm²), 7/28 (7x0,32mm), Insulation Thickness: 0.016" (0,41mm)					
XTRA•GUARD 4 Part No.	No. of Pairs	Jacket Thickness Inches mm		Nominal Diameter Inches mm	
45291 45292 45293 45294 45295 45296 45299 45299/11 45299/15	1 2 3 4 5 6 9 11	0.045 0.045 0.045 0.055 0.055 0.055 0.055 0.065	1,14 1,14 1,14 1,40 1,40 1,40 1,40 1,65 1,65	0.261 0.351 0.369 0.419 0.452 0.487 0.559 0.620 0.694	6,63 8,92 9,37 10,64 11,48 12,37 14,20 15,75 17,63

18 AWG (0,81mm²), 16/30 (16x0,25mm), Insulation Thickness: 0.016" (0,41mm)					
XTRA•GUARD 4 Part No.	No. of Pairs	Jacket Th Inches	ickness mm	Nominal I Inches	Diameter mm
▲ 45131 ▲ 45132 45133 45134 45135 45136 45139 45139/11 45139/15	1 2 3 4 5 6 9 11	0.045 0.045 0.055 0.055 0.055 0.055 0.065 0.065	1,14 1,14 1,40 1,40 1,40 1,40 1,65 1,65	0.279 0.380 0.420 0.454 0.492 0.532 0.632 0.685 0.762	7,09 9,65 10,67 11,53 12,50 13,51 16,05 17,40 19,35

#### FIT® TUBING RECOMMENDATION

FIT -600 — Highly Flexible, Irradiated Elastomer (See Page 131 for Product Specifications)
FIT -400 — Temperature/Chemical Resistant FEP Teflon®

(See Page 129 for Product Specifications)



# TECHNICAL DATA

# **COLOR CODE CHARTS**

## **MULTIPAIR CABLES**

CHART A			
Pair Color No. Combination	Pair Color No. Combination	Pair Color No. Combination	Pair Color No. Combination
1 — Black paired with Red 2 — Black paired with White 3 — Black paired with Green 4 — Black paired with Blue 5 — Black paired with Brown 6 — Black paired with Vellow 7 — Black paired with Orange 8 — Red paired with Green 9 — Red paired with White 10 — Red paired with Blue 11 — Red paired with Blue 12 — Red paired with Brown 13 — Red paired with Orange	14 — Green paired with Blue 15 — Green paired with White 16 — Green paired with Brown 17 — Green paired with Orange 18 — Green paired with Yellow 19 — White paired with Blue 20 — White paired with Brown 21 — White paired with Orange 22 — White paired with Yellow 23 — Blue paired with Brown 24 — Blue paired with Orange 25 — Blue paired with Orange 26 — Brown paired with Orange	27 — Brown paired with Yellow 28 — Purple paired with Red 29 — Purple paired with White 30 — Purple paired with Green 31 — Purple paired with Blue 32 — Purple paired with Brown 33 — Purple paired with Yellow 34 — Purple paired with Orange 35 — Purple paired with Orange 36 — Purple paired with Black 37 — Slate paired with Red 38 — Slate paired with White 39 — Slate paired with Green	40 — Slate paired with Blue 41 — Slate paired with Brown 42 — Slate paired with Yellow 43 — Slate paired with Orange 44 — Slate paired with Black 45 — White/Black paired with Green 47 — White/Black paired with Blue 48 — White/Black paired with Brown 49 — White/Black paired with Yellow 50 — White/Black paired with Orange 51 — White/Black paired with Purple

CHART B			
Pair Color No. Combination	Pair Color No. Combination	Pair Color No. Combination	Pair Color No. Combination
1 — White paired with Black 2 — White paired with Brown 3 — White paired with Red 4 — White paired with Orange 5 — White paired with Orange 6 — White paired with Green 7 — White paired with Blue 8 — White paired with Violet 9 — White paired with Brown 11 — Black paired with Brown 11 — Black paired with Red 12 — Black paired with Orange 13 — Black paired with Orange 13 — Black paired with Green 15 — Black paired with Green 15 — Black paired with Green 16 — Black paired with Violet 17 — Black paired with Violet 18 — Brown paired with Red 19 — Brown paired with Red 19 — Brown paired with Orange 20 — Brown paired with Green 21 — Brown paired with Green 22 — Brown paired with Green 23 — Brown paired with Green 24 — Brown paired with Green 25 — Red paired with Gray 26 — Red paired with Orange	27 — Red paired with Green 28 — Red paired with Blue 29 — Red paired with Violet 30 — Red paired with Gray 31 — Orange paired with Green 32 — Orange paired with Green 33 — Orange paired with Blue 34 — Orange paired with Blue 34 — Orange paired with Gray 36 — Yellow paired with Gray 36 — Yellow paired with Gray 37 — Yellow paired with Blue 38 — Yellow paired with Blue 39 — Yellow paired with Gray 40 — Green paired with Gray 40 — Green paired with Violet 41 — Green paired with Violet 42 — Green paired with Gray 43 — Blue paired with Gray 45 — Violet paired with Gray 46 — White/Black paired with Brown 48 — White/Black paired with Brown 48 — White/Black paired with Red 49 — White/Black paired with Crange 50 — White/Black paired with Green 51 — White/Black paired with Green 52 — White/Black paired with Green	53 — White/Black paired with Violet 54 — White/Black paired with Gray 55 — White/Brown paired with Black 56 — White/Brown paired with Brown 57 — White/Brown paired with Red 58 — White/Brown paired with Orange 59 — White/Brown paired with Yellow 60 — White/Brown paired with Yellow 60 — White/Brown paired with Blue 62 — White/Brown paired with Gray 64 — White/Brown paired with Gray 64 — White/Red paired with Brown 66 — White/Red paired with Brown 66 — White/Red paired with Orange 68 — White/Red paired with Orange 68 — White/Red paired with Gray 70 — White/Red paired with Green 70 — White/Red paired with Green 70 — White/Red paired with Gray 71 — White/Proange paired with Black 72 — White/Orange paired with Black 73 — White/Orange paired with Brown 74 — White/Orange paired with Brown 75 — White/Orange paired with Orange 77 — White/Orange paired with Orange	78 — White/Orange paired with Green 79 — White/Orange paired with Blue 80 — White/Orange paired with Violet 81 — White/Orange paired with Gray 82 — White/Yellow paired with Black 83 — White/Yellow paired with Brown 84 — White/Yellow paired with Red 85 — White/Yellow paired with Orange 86 — White/Yellow paired with Green 88 — White/Yellow paired with Green 89 — White/Yellow paired with Green 89 — White/Yellow paired with Gray 90 — White/Green paired with Blue 90 — White/Green paired with Brown 91 — White/Green paired with Brown 93 — White/Green paired with Green 94 — White/Green paired with Green 95 — White/Green paired with Green 96 — White/Green paired with Green 97 — White/Green paired with Green 97 — White/Green paired with Green 98 — White/Green paired with Gray 100 — White/Green paired with Blue 99 — White/Green paired with Blue 99 — White/Green paired with Gray 100 — White/Blue paired with Brown 101 — White/Blue paired with Brown 102 — White/Blue paired with Brown 103 — White/Blue paired with Brown 104 — White/Blue paired with Brown 105 — White/Blue paired with Brown 106 — White/Blue paired with Brown 107 — White/Blue paired with Brown 108 — White/Blue paired with Brown 109 — White/Blue paired with Brown 100 — White/Blue paired with Brown

26 – Red paired with Yellow	52 – White/Black paired with Blue		
CHART C			
Pair Color No. Combination	Pair Color No. Combination	Pair Color No. Combination	Pair Color No. Combination
1 — Blue paired with White 2 — Orange paired with White 3 — Green paired with White 4 — Brown paired with White 5 — Slate paired with White 6 — Blue/White paired with White 7 — Blue/Orange paired with White 8 — Blue/Green paired with White 9 — Blue/Brown paired with White 10 — Blue/Slate paired with White 11 — Orange/White paired with White 12 — Orange/Green paired with White 13 — Orange/Brown paired with White	14 — Orange/Slate paired with White 15 — Green/White paired with White 16 — Green/Brown paired with White 17 — Green/Slate paired with White 18 — Brown/White paired with White 19 — Brown/Slate paired with White 20 — Slate/White paired with White 21 — Blue paired with Red 22 — Orange paired with Red 23 — Green paired with Red 24 — Brown paired with Red 25 — Slate paired with Red 26 — Blue/White paired with Red	27 — Blue/Orange paired with Red 28 — Blue/Green paired with Red 29 — Blue/Brown paired with Red 30 — BLue/Slate paired with Red 31 — Orange/White paired with Red 32 — Orange/Green paired with Red 33 — Orange/Brown paired with Red 34 — Orange/Slate paired with Red 35 — Green/White paired with Red 36 — Green/Brown paired with Red 37 — Green/Slate paired with Red 38 — Brown/White paired with Red 39 — Brown/Slate paired with Red	40 — Slate/White paired with Red 41 — Blue paired with Black 42 — Orange paired with Black 43 — Green paired with Black 44 — Brown paired with Black 45 — Slate paired with Black 46 — Blue/White paired with Black 47 — Blue/Orange paired with Black 48 — Blue/Green paired with Black 49 — Blue/Brown paired with Black 50 — Blue/Slate paired with Black 51 — Orange/White paired with Black

