

Resistance Soldering

Resistance Soldering Systems - Tweezer-Style



Light Capacity
Tweezer-Style Resistance Soldering System
Model 10501

Common Applications: Micro miniature setups, wire processing, terminations, small connections.

Components:

- 105A3 100 Watt Resistance Soldering Power Unit
- 10541 Regular Tweezer Handpiece
- 10519 Footswitch

Specifications:

- 100W (2.65VAC) Power unit with Infinitely Variable Output control, Pilot light, 1 AMP Circuit Protection & Heavy-duty aluminum case, Available in 110 or 220V.
- Durable, User-friendly hand piece with four foot (1.22m) AWG 14-2 HPN cord set.
- Copper clad, stainless steel electrodes, 5/64" (1.98mm) Dia., 1 ½" Lgth. Easily customizable with approx. 3/8" opening upon shipping.
- Rugged, Industrial Footswitch with 6 foot (1.83m), three-wire cord and NEMA 5-15 P/ R piggyback plug.

Weight: 5.5LBS (2.475KGS)

Replacement Electrodes: Model # 10542

See Product Data Sheet



Standard Capacity
Tweezer-Style Resistance Soldering System
Model 10502

Common Applications: Wire processing, terminations, fiber optics, standard connections, electrical, electronics work.

Components:

- 105A12 250 Watt Resistance Soldering Power Unit
- 10541 Regular Tweezer Handpiece
- 10519 Footswitch

Specifications:

- 250W (2.8VAC) Power unit with Infinitely Variable Output control, Lighted Rocker, 3 AMP Circuit Breaker & Heavy-duty aluminum case, Available in 110 or 220V.
- Durable, User-friendly hand piece with four foot (1.22m) AWG 14-2 HPN cord set.
- Copper clad, stainless steel electrodes, 5/64" (1.98mm) Dia., 1 ½" Lgth. Easily customizable with approx. 3/8" opening upon shipping.
- Rugged, industrial Footswitch with 6 foot (1.83m), three-wire cord and NEMA 5-15 P/ R piggyback plug.

Weight: 9.3LBS (4.185KGS)

Replacement Electrodes: Model # 10542

See Product Data Sheet



High Capacity
Tweezer-Style Resistance Soldering System
Model 10504

Common Applications: Antenna leads and semi-rigid coaxial cable, connections up to ¼" (6.5mm), heavy gauge wire, terminals, lugs, posts, heavy-duty soldering.

Components:

- 105A12 250 Watt Resistance Soldering Power Unit
- 105127 Medium Tweezer Handpiece
- 10519 Footswitch

Specifications:

- 250W (2.8VAC) Power unit with Infinitely Variable Output control, Lighted Rocker, Circuit Breaker & Heavy-duty aluminum case, Available in 110 or 220V.
- Durable, User-friendly hand piece with four foot (1.22m) 10 AWG High Strand DLO cord set
- Copper clad, stainless steel electrodes, 1/8" (1.98mm) Dia., 3" Lgth. Easily customizable with approx. 1" opening upon shipping.
- Rugged, industrial Footswitch with 6 foot (1.83m), three-wire cord and NEMA 5-15 P/ R piggyback plug.

Weight: 9.7LBS (4.365KGS)

Replacement Electrodes: Model # 10594

See Product Data Sheet



Micro Tweezer-Style Resistance Soldering System Model 10599

Common Applications: For micro-soldering applications in limited space. Fine AWG wire processing, terminations, very small connections.

Components:

- 105A3 100 Watt Resistance Soldering Power Unit
- 105133 Micro-Tweezer Handpiece
- 10519 Footswitch

Specifications:

- 100W (2.65VAC) Power unit with Infinitely Variable Output control, Pilot light, 1 AMP Circuit Protection & Heavy-duty aluminum case, Available in 110 or 220V.
- Durable, User-friendly hand piece with four foot (1.22m) AWG 18-2 HPN cord set.
- Stainless steel electrodes, .040" (1.02mm) Dia., 1/2" Lgth. Easily customizable by forming or notching.
- Rugged, industrial Footswitch with 6 foot (1.83m), three-wire cord and NEMA 5-15 P/ R piggyback plug.

Weight: 5.5LBS (2.475KGS)

Replacement Electrodes: Model # 105134

See Product Data Sheet

1177 West Maple Road Clawson, MI 48017-1059 **United States** (800) 550-2510 (248) 280-2810

Fax: (248) 280-2878