/ American



Home Find your Tool Technical Support Learn about Soldering Heavy-Duty Soldering Irons Quote Cart Resistance Soldering Solder Pots Desoldering Braid **VIDEO LIBRARY Products** Video Library Products > All Heavyirons > 3138 SEARCH By Type of User: Filter by: + Select... Diameter: Select... \$ Go! By Type of Application: Select... +) 100, 130 or 150-Watt Heavy-Duty Soldering Iron By Keyword: Model: 3138 Go Standard Tips: **TO PURCHASE** 43D - Paragon Soldering Iron Tips Request A Quote **Primary Alternative: USA Distribution** 43C - Paragon Soldering Iron Tips International Distributors Alternate Tips: Sales Representatives 823 - **Discontinued** Paragon Soldering Iron Tip Becoming a Distributor 830 - **Discontinued** Paragon Soldering Iron Tip Contact Us Applications: DOWNLOADS Soldering stained glass applications Soldering cover to enclosure on electronic assemblies for aircraft applications. Catalog Specifications: WATTAGE - 100, 130, 150 Watts REPLACEMENT HEATING ELEMENT NUMBER - 9273 MAXIMUM TIP TEMPERATURE (F) - 855°F, 955°F, 1010°F MAXIMUM TIP TEMPERATURE (C) - 457°C, 513°C, 543°C OVERALL LENGTH - 12 7/8" (32.7cm) TIP SHANK DIAMETER - 3/8" (9.5mm) TIP LENGTH - 4 3/8" (11.1cm) PRODUCT WEIGHT - 13 oz. (.37 kg) SHIPPING WEIGHT - 2 lbs. (.91 kg) Diameter: 3/8

American Beauty Soldering Tools are proudly manufactured by Assembly Technologies International, Inc.

O Add to Quote - Product Link

1177 West Maple Road Clawson, MI 48017-1059 United States -- Phone: 800-550-2510