



Description

American Beauty offers the widest selection of resistance soldering handpieces in the world. Our hand pieces are designed and built to provide absolute performance in even the toughest environments. By generating heat instantaneously and right at the point of contact, you are able to easily handle the historically difficult soldering jobs.

Related Products

The following products are related (similar model but different specifications, etc.) to Model 105158 featured on this page:

Model	Product Name
10506	Light Capacity Plier-Style Resistance Soldering System

Replacement Products

The following products can be used as replacements for Model 105158 featured on this page:

Model	Product Name
105159	Small Carbon Block Electrodes for Resistance Soldering

Applications

Technical Specifications

RoHS Compliant	Yes
Connection Type	Tapered Pins
Electrode Size/Diameter	.25 in / 0.64 cm
Opening between Electrodes	.25 in / 0.64 cm
Product Length	5 in / 12.70 cm
Country of Origin	US
Package Length	9.50 in / 24.13 cm
Package Width	2.00 in / 5.08 cm
Package Height	2.00 in / 5.08 cm
Shipping Weight	.60 lbs / 0.27 kg

User Information and Instruction Sheet

Other Product Data Sheets

Features and Benefits

Carbon block electrodes can be easily notched/shaped, allowing the user to customize the handpiece to their specific application.