



Description

A resistance soldering system is only as good as your 'Point of Contact'. American Beauty incorporates only the highest quality electrodes and elements into our hand pieces. All carbon and stainless steel electrodes are copper-clad for improved current flow, except for Models 10565, 10566, 105134 & 105159 whose short lengths don't require such measures. Inferior quality electrodes and elements will affect overall system performance and could void applicable warranties.

Related Products

The following products are related (similar model but different specifications, etc.) to Model 10525 featured on this page:

Model	Product Name
10573	3/16" Carbon Probe Style Handpiece

Replacement Products

Applications

Users of this product have stated that they use it for several jobs which include but are not limited to:

1. Repairing electronic assembly

Technical Specifications

RoHS Compliant	Yes
Tip Configuration	Blunt Conical
Tip Diameter	3/16 in / 7.62 cm
Tip Length	3 in / 7.62 cm
Width of Working Area	.078 in / 0.20 cm
Tapered Distance of Working Area	1/4 in / 2.54 cm
Understanding Tip Measurements	Explanation
Country of Origin	US
Package Length	3.00 in / 7.62 cm
Package Width	1.25 in / 3.18 cm
Package Height	.25 in / 0.64 cm
Shipping Weight	.05 lbs / 0.02 kg

User Information and Instruction Sheet

Other Product Data Sheets

Features and Benefits