



Description

A resistance soldering system is only as good as your 'Point of Contact'. American Beauty incorporates only the highest quality electrodes and elements into our hand pieces. All carbon and stainless steel electrodes are copper-clad for improved current flow, except for Models 10565, 10566, 105134 & 105159 whose short lengths don't require such measures. Inferior quality electrodes and elements will affect overall system performance and could void applicable warranties.

Related Products

The following products are related (similar model but different specifications, etc.) to Model 10566 featured on this page:

Model	Product Name	
10588	1/2" Dual Probe Style Handpiece	

Replacement Products

Applications

Technical Specifications

RoHS Compliant	Yes
Tip Configuration	Block
Tip Length	1.5 in / 3.81 cm
Width of Working Area	.4 in / 1.02 cm
Understanding Tip Measurements	Explanation
Country of Origin	US
Package Length	2.50 in / 6.35 cm
Package Width	1.50 in / 3.81 cm
Package Height	.50 in / 1.27 cm
Shipping Weight	.05 lbs / 0.02 kg

User Information and Instruction Sheet

Other Product Data Sheets

Features and Benefits