



Description

American Beauty offers the widest selection of resistance soldering handpieces in the world. Our hand pieces are designed and built to provide absolute performance in even the toughest environments. By generating heat instantaneously and right at the point of contact, you are able to easily handle the historically difficult soldering jobs.

Related Products

The following products are related (similar model but different specifications, etc.) to Model 10578 featured on this page:

Model	Product Name
10501	Ultra-Light Capacity Tweezer-Style Resistance Soldering System
10502	Light Capacity Tweezer-Style Resistance Soldering System

Replacement Products

The following products can be used as replacements for Model 10578 featured on this page:

Model	Product Name
10582	5/64" Steel Electrodes for Resistance Soldering

Applications

Technical Specifications

RoHS Compliant	Yes
Connection Type	Tapered Pins
Electrode Size/Diameter	.078 in / 0.20 cm
Opening between Electrodes	.125 in / 0.32 cm
Product Length	6 in / 15.24 cm
Country of Origin	US
Package Length	9.50 in / 24.13 cm
Package Width	2.00 in / 5.08 cm
Package Height	2.00 in / 5.08 cm
Shipping Weight	.50 lbs / 0.23 kg

User Information and Instruction Sheet

Other Product Data Sheets

Features and Benefits

Copper-coated, stainless steel electrodes can be easily bent, allowing the user to customize the handpiece to their specific application.