



Description

A resistance soldering system is only as good as your 'Point of Contact'. American Beauty incorporates only the highest quality electrodes and elements into our hand pieces. All carbon and stainless steel electrodes are copper-clad for improved current flow, except for Models 10565, 10566, 105134 & 105159 whose short lengths don't require such measures. Inferior quality electrodes and elements will affect overall system performance and could void applicable warranties.

Related Products

The following products are related (similar model but different specifications, etc.) to Model 10582 featured on this page:

| Model | Product Name | |
|-------|----------------------------------|--|
| 10552 | 5/64" Probe Style Handpiece | |
| 10578 | 5/64" Fixed Dual Probe Handpiece | |

Replacement Products

Applications

Technical Specifications

| | |
|----------------------------------|--------------------|
| RoHS Compliant | Yes |
| Tip Configuration | Conical |
| Tip Diameter | 5/64 in / 12.70 cm |
| Tip Length | 3 in / 7.62 cm |
| Width of Working Area | .02 in / 0.05 cm |
| Tapered Distance of Working Area | 1/4 in / 2.54 cm |
| Understanding Tip Measurements | Explanation |
| Country of Origin | US |
| Package Length | 2.50 in / 6.35 cm |
| Package Width | 1.00 in / 2.54 cm |
| Package Height | .25 in / 0.64 cm |
| Shipping Weight | .01 lbs / 0.00 kg |

User Information and Instruction Sheet

Other Product Data Sheets

Features and Benefits