

Replacement Products


Resistance Soldering Handpieces

American Beauty[®] offers the WIDEST SELECTION of Resistance Soldering and Wirestripping Handpieces in the World!

Our hand pieces are designed and built to provide absolute performance in even the toughest environments.

Resistance Soldering and Wirestripping hand pieces provide instantaneous localized heat to help you handle all of your difficult soldering needs.

- Adhere to 50% duty cycle during all applications to ensure handpiece longevity.
- Ensure that handpiece shares the same connection style as the power unit with which it is to be used.
- Virtually every handpiece can be customized to your specific needs. Phone us directly with specific requests.



Micro-Tweezer Handpiece Model 105133

Lightweight tool designed for micro-soldering applications in limited space; well suited for work on connections with wire 22 AWG and finer.

Included in system:

• 10599 - Micro Tweezer-Style Resistance Soldering System

Specifications:

- 61/2" (16.5cm) total length, 4 ft. cord
- Copper-clad, stainless steel electrodes, .040" (1.02mm) diameter
- Electrodes may be formed, notched or gound to fit specific applications
- Taper pin connection style

Weight: 0.5LBS (0.225KGS)

Replacement Electrodes: Model # 105134

See Product Data Sheet



Regular Tweezer Handpiece Model 10541

Ideal tool for intricate soldering applications, combining intense heat with precise contact points.

Included in systems:

- 10501 Light Capacity Tweezer-Style Resistance Soldering System
- 10502 Standard Capacity Tweezer-Style Resistance Soldering System
- 105HCS Light Capacity Resistance Soldering Hobby System
- 105HCM Standard Capacity Resistance Soldering Hobby System
- 105HHH Deluxe Resistance Soldering Hobby System

Specifications:

- 5" (12.7cm) total length, 4 ft. cord
- Taper Pin connection style
- Copper-clad, stainless steel electrodes .078" (1.98mm) diameter


• Electrodes may be formed, notched or ground to fit specific applications

• Space between electrodes is 3/8" (9.53mm)before any modifications

Weight: 1.0LBS (0.45KGS)

Replacement Electrodes: Model # 10542

See Product Data Sheet



Medium Tweezer Handpiece Model 105127

Our most popular tool this rugged performer is excellent for antenna leads, semi-rigid co-ax, heavy-gauge wire, terminals, lugs, posts, etc.

Included in system:

• 10504 - High Capacity Tweezer-Style Resistance Soldering System

Specifications:

- 7" (17.75cm) total length, 4 ft. 10 AWG high-strand DLO cable
- Copper-clad, stainless steel electrodes, .125" (3.18mm) diameter
- Approxiamate 1/2" opening between electrodes upon shipping
- Electrodes may be formed, notched or gound to fit specific applications
- Taper pin connection style

Weight: 2.0LBS (0.9KGS)



Ultra-Light Fixed
Dual-Electrode Handpieces
Model 10578

Ideal when absolute repeatability is desired.

Specifications:

- 6" (15.3cm) total length, 4 ft. cord
- Taper Pin connection style
- Copper-clad, stainless steel electrodes .078" (1.98mm) diameter
- Electrodes may be formed, notched or ground to fit specific applications
- Space between electrodes is 1/8" (3.25mm)before any modifications

Weight: 1.0LBS (0.45KGS)



Regular Dual-Electrode Soldering Handpiece Model 10590

Ideal when repeatability is desired

Specifications:

- 7½" (19cm) total length, 4 ft. 10 AWG high-strand DLO cable
- Copper-clad, stainless steel electrodes, .125" (3.18mm) diameter
- Approxiamate 3/8" opening between electrodes upon shipping
- Electrodes may be formed, notched or gound to fit specific applications
- Taper pin connection style

Weight: 1.5LBS (0.675KGS)



Single Carbon Handpiece

Model 10515

Lightweight tool for soldering in areas inaccessible to tweezer style handpieces. Perfect for seems & spots.

Included in systems:

- 10508 Light Capacity Single Probe Resistance Soldering System
- 105HCS Light Capacity Resistance Soldering Hobby System
- 105HCM Standard Capacity Resistance Soldering Hobby System
- 105HHH Deluxe Resistance Soldering Hobby System

Specifications:

- 6"(15.3cm) total length, 4 ft. cord
- Supplied with 3/32" (2.38mm) diameter copper-clad carbon electrodes
- Ground Lead Required, Model 10512A recommended
- Taper pin connection style

Weight: 1.0LBS (0.45KGS)

Replacement Electrodes: Model # 10530



Standard 1/4"
Diameter Single Carbon Handpiece
Model 10511

Sturdy single carbon tool designed to handle a general assortment of soldering applications, rework and repair.

Included in system:

• 10509 - High Capacity Single Probe Resistance Soldering System

Specifications:

- 8" (20.4cm) total length, 4 foot cord
- Return lead is required, Model 10512 recommended
- Accepts electrodes either straight or at a 45° angle
- Supplied with 1/4" diameter copper clad carbon electrode.
- Taper pin connection style

Weight: 1.0LBS (0.45KGS)

Replacement Electrodes: Model # 10549

See Product Data Sheet



1/8" Diameter Single Carbon Handpiece Model 10572

Lightweight handpiece for micro-soldering in areas inaccessible to tweezer style handpieces.

Specifications:

- 6"(15.3cm) total length, 4 ft (1.22m) cord
- Ground Lead required, Model 10512A recommended
- .125" (3.18mm) diameter copper-clad carbon electrodes that may be ground to fit specific applications.
- Taper pin connection style

Weight: 1.0LBS (0.45KGS)



3/16" Diameter Single Carbon Handpiece

Model 10573

Lightweight tool for soldering in areas inaccessible to tweezer-style handpieces

Specifications:

- 6"(15.3cm) total length, 4 ft. cord
- Ground Lead required, Model 10512A recommended
- 3/16" (3.18mm) diameter copper-clad carbon electrodes that may be ground to fit specific applications.
- Taper pin connection style

Weight: 1.0LBS (0.45KGS)

Replacement Electrodes: Model # 10525



5/64" Diameter Single Stainless Steel Handpiece Model 10552

Lightweight handpiece for micro-soldering in areas inaccessible to tweezers handpieces.

Specifications:

- 6"(15.3cm) total length, 4 ft. cord
- Ground Lead required, 10512A recommended
- 5/64" (2.0mm) diameter copper-clad stainless steel electrodes that may be formed, notched or ground to fit specific applications.
- Taper pin connection style

Weight: 1.0LBS (0.45KGS)

Replacement Electrodes: Model # 10582



1/2" Diameter Heavy-Duty Single Carbon Handpiece Model 10536

Rugged tool designed to handle your extra heavy work.


Specifications:

- 7½"(19.1cm) total length, 4 ft (1.22m)
- $\frac{1}{2}$ " (12.7mm) diameter copper-clad carbon electrodes that may be ground to fit specific applications.
- Ring Terminal connection style
- Ground Lead required, Model 10537 recommended

Weight: 2.0LBS (0.9KGS)

Replacement Electrodes: Model # 10534

See Product Data Sheet



Small High-Heat
Carbon Pliers Handpiece
Model 105158

Carbon electrodes provide you more intense heat than our standard copper-clad stainless steel. Ideal for applications involving small sized parts (3/16") but large heat-sinks.

Included in system:

• 10506 - Standard Capacity Plier-Style Resistance Soldering System

Specifications:

- 5"(12.7cm) total length, 4 ft (1.22m)
- Taper Pin connection style
- Ring Terminal attachement style available upon request

Weight: 2.0LBS (0.9KGS)



Carbon Pliers Handpiece

Model 105258

This is a heavy-duty version of the Model 105158 to better handle the higher current loads required for some larger industrial applications.

Included in system:

• 10507 - High Capacity Plier-Style Resistance Soldering System

Specifications:

- 7"(17.75cm) total length, 4 ft (1.22m) cord
- Taper Pin connection style
- Ring Terminal attachement style available upon request
- Compatible with 105C1 Power Unit and higher with modification to Ring Terminal attachement style

Weight: 2.5LBS (1.125KGS)

Replacement Electrodes: Model # 105159



Heavy-Duty High-Heat Carbon Pliers Handpiece Model 10587

Based upon internal testing and customer response these are the highest quality & best performing large resistance soldering handpiece available on the market today.

Included in systems:

- 10505 Industrial Capacity Plier-Style Resistance Soldering System
- 10557 Medium-Duty Resistance Soldering Plumbing System
- 10577 Heavy-Duty Resistance Soldering Plumbing System

Specifications:

• Please adhere to 50% Duty Cycle

- Length 10"(25.4cm), 10ft (3.05m)
- Connects to Power Unit via Ring Terminals

Weight: 5.0LBS (2.25KGS)

Replacement Electrodes: Model # 10565



Heavy-Duty Carbon Fork-Type Handpiece Model 10588

A modification of our popular Model 10587 handpiece. Based upon internal testing and customer response these are the highest quality & best performing large resistance soldering handpiece available on the market today.

Specifications:

- Connects to Power Unit via Ring Terminals
- Length 10"(25.4cm), 10ft (3.05m)
- Please adhere to 50% Duty Cycle

Weight: 5.0LBS (2.25KGS)